

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300722

Luminaire Tested: P3AS17R35W2N902765DE010 E3DLP1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300722
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R35W2N902765DE010 E3DLP1WH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1138.0 lumens
Efficiency: N/A
Efficacy: 58.7 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300722
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLP1WH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1300722

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLP1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	67
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	573967
5°	551616
10°	480619
15°	368129
20°	246281
25°	149017
30°	85507
35°	47810
40°	25419
45°	13087
50°	6277
55°	4970
60°	4736
65°	3943
70°	4167
75°	3643
80°	4041
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13087 cd/sqm



TEST NUMBER: P1300722

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLP1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.0	20.0
10°-20°	441.8	38.8
20°-30°	289.3	25.4
30°-40°	117.4	10.3
40°-50°	35.2	3.1
50°-60°	12.0	1.1
60°-70°	8.0	0.7
70°-80°	4.7	0.4
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	959.1	84.3
0°-40°	1076.5	94.6
0°-60°	1123.6	98.7
0°-90°	1138.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1138.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2618	
5°	2506	228
15°	1622	442
25°	616	289
35°	179	117
45°	42	35
55°	13	12
65°	8	8
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P1300722

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLP1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2617.5
1°	2613.1
2°	2601.2
3°	2577.4
4°	2549.3
5°	2506.0
6°	2451.8
7°	2391.2
8°	2323.0
9°	2245.1
10°	2158.5
11°	2062.1
12°	1961.5
13°	1848.9
14°	1741.7
15°	1621.6
17.5°	1330.4
20°	1055.4
22.5°	811.9
25°	615.9
27.5°	459.0
30°	337.7
32.5°	247.9
35°	178.6
37.5°	126.7
40°	88.8
42.5°	61.7
45°	42.2
47.5°	28.1
50°	18.4
52.5°	14.1
55°	13.0
57.5°	11.9
60°	10.8
62.5°	9.7
65°	7.6
67.5°	6.5
70°	6.5
72.5°	5.4
75°	4.3
77.5°	3.2
80°	3.2
82.5°	2.2
85°	1.1
87.5°	1.1



TEST NUMBER: P1300722
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLP1WH_2700K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)