

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298352

Luminaire Tested: P3AS13R60W2N902765DE010 E3CD1MB\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298352  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R60W2N902765DE010 E3CD1MB\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,  
E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 896.1 lumens  
Efficiency: N/A  
Efficacy: 72.8 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298352  
CATALOG NUMBER: P3AS13R60W2N902765DE010 E3CD1MB\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1298352

CATALOG NUMBER: P3AS13R60W2N902765DE010 E3CD1MB\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94				94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87				87
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81				81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76				76
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71				71
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	68	66				66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62				62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58				58
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55				55
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51				51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	213952
5°	205480
10°	211553
15°	214280
20°	189203
25°	159445
30°	129311
35°	84216
40°	38672
45°	14823
50°	4981
55°	1338
60°	1228
65°	1090
70°	898
75°	1186
80°	884
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14823 cd/sqm



TEST NUMBER: P1298352

CATALOG NUMBER: P3AS13R60W2N902765DE010 E3CD1MB\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.8	10.0
10°-20°	258.5	28.8
20°-30°	301.5	33.6
30°-40°	194.5	21.7
40°-50°	43.6	4.9
50°-60°	4.4	0.5
60°-70°	2.1	0.2
70°-80°	1.2	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	649.8	72.5
0°-40°	844.3	94.2
0°-60°	892.3	99.6
0°-90°	896.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	896.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	976	
5°	934	90
15°	944	258
25°	659	301
35°	315	195
45°	48	44
55°	4	4
65°	2	2
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P1298352  
CATALOG NUMBER: P3AS13R60W2N902765DE010 E3CD1MB\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	975.7
2.5°	959.8
5°	933.5
7.5°	932.1
10°	950.1
12.5°	961.9
15°	943.9
17.5°	889.8
20°	810.8
22.5°	728.3
25°	659.0
27.5°	591.1
30°	510.7
32.5°	416.5
35°	314.6
37.5°	214.8
40°	135.1
42.5°	81.1
45°	47.8
47.5°	27.7
50°	14.6
52.5°	4.9
55°	3.5
57.5°	2.8
60°	2.8
62.5°	2.1
65°	2.1
67.5°	2.1
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)