

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298404

Luminaire Tested: P3AS13R60W2N902765DE010 E3DL1GPH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298404  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R60W2N902765DE010 E3DL1GPH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 398.0 lumens  
Efficiency: N/A  
Efficacy: 32.4 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298404  
CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DL1GPH\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1298404

CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DL1GPH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.8	10.0
10°-20°	103.5	26.0
20°-30°	118.0	29.6
30°-40°	83.6	21.0
40°-50°	38.0	9.5
50°-60°	8.1	2.0
60°-70°	3.9	1.0
70°-80°	2.4	0.6
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	261.3	65.6
0°-40°	344.9	86.7
0°-60°	390.9	98.2
0°-90°	398.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	398.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	429	
5°	423	40
15°	373	103
25°	259	118
35°	133	84
45°	48	38
55°	6	8
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1298404  
CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DL1GPH\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	428.6
2.5°	427.1
5°	422.9
7.5°	415.7
10°	405.9
12.5°	391.9
15°	373.0
17.5°	349.1
20°	321.2
22.5°	290.9
25°	259.1
27.5°	226.6
30°	194.1
32.5°	163.0
35°	133.2
37.5°	106.7
40°	82.8
42.5°	62.8
45°	47.7
47.5°	35.6
50°	23.5
52.5°	11.0
55°	6.1
57.5°	5.3
60°	4.9
62.5°	4.5
65°	3.8
67.5°	3.4
70°	3.0
72.5°	2.6
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)