

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298589

Luminaire Tested: P3AS13R65W2N902750DE010 E3DL1WMH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298589  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRIS  
Catalog Number: P3AS13R65W2N902750DE010 E3DL1WMH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,  
E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 767.0 lumens  
Efficiency: N/A  
Efficacy: 62.4 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298589  
CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DL1WMH\_3000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1298589

CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DL1WMH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.2	9.9
10°-20°	197.4	25.7
20°-30°	230.8	30.1
30°-40°	161.3	21.0
40°-50°	71.0	9.3
50°-60°	15.8	2.1
60°-70°	8.0	1.0
70°-80°	4.9	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	504.4	65.8
0°-40°	665.7	86.8
0°-60°	752.5	98.1
0°-90°	767.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	767.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	825	
5°	812	76
15°	709	197
25°	508	231
35°	256	161
45°	89	71
55°	13	16
65°	8	8
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1298589  
CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DL1WMH\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	824.9
2.5°	821.8
5°	811.9
7.5°	795.1
10°	772.1
12.5°	743.8
15°	709.4
17.5°	667.4
20°	620.8
22.5°	568.0
25°	508.4
27.5°	445.7
30°	380.0
32.5°	316.5
35°	256.1
37.5°	203.4
40°	156.7
42.5°	118.5
45°	89.4
47.5°	65.7
50°	41.3
52.5°	21.4
55°	13.0
57.5°	11.5
60°	9.9
62.5°	9.2
65°	8.4
67.5°	6.9
70°	6.1
72.5°	5.4
75°	4.6
77.5°	3.8
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)