

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300838

Luminaire Tested: P3AS17R40W2N902750DE010 E3DLD1GPH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1300838  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R40W2N902750DE010 E3DLD1GPH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 523.0 lumens  
Efficiency: N/A  
Efficacy: 27.0 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300838  
CATALOG NUMBER: P3AS17R40W2N902750DE010 E3DLD1GPH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1300838

CATALOG NUMBER: P3AS17R40W2N902750DE010 E3DLD1GPH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	117403
5°	115276
10°	108660
15°	98707
20°	86714
25°	74037
30°	61326
35°	47301
40°	33663
45°	22669
50°	12383
55°	8717
60°	8201
65°	7575
70°	6732
75°	6439
80°	5177
85°	4529

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22669 cd/sqm



TEST NUMBER: P1300838

CATALOG NUMBER: P3AS17R40W2N902750DE010 E3DLD1GPH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.8	9.3
10°-20°	121.1	23.2
20°-30°	140.0	26.8
30°-40°	110.3	21.1
40°-50°	56.6	10.8
50°-60°	21.6	4.1
60°-70°	14.3	2.7
70°-80°	7.8	1.5
80°-90°	2.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	309.9	59.3
0°-40°	420.3	80.4
0°-60°	498.5	95.3
0°-90°	523.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	523.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	535	
5°	524	49
15°	435	121
25°	306	140
35°	177	110
45°	73	57
55°	23	22
65°	15	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1300838  
CATALOG NUMBER: P3AS17R40W2N902750DE010 E3DLD1GPH\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	535.4
2.5°	532.5
5°	523.7
7.5°	508.5
10°	488.0
12.5°	464.0
15°	434.8
17.5°	404.3
20°	371.6
22.5°	338.2
25°	306.0
27.5°	273.8
30°	242.2
32.5°	210.1
35°	176.7
37.5°	145.7
40°	117.6
42.5°	93.6
45°	73.1
47.5°	53.2
50°	36.3
52.5°	26.3
55°	22.8
57.5°	20.5
60°	18.7
62.5°	16.4
65°	14.6
67.5°	12.3
70°	10.5
72.5°	8.8
75°	7.6
77.5°	5.9
80°	4.1
82.5°	3.5
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)