

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298683

Luminaire Tested: P3AS13R65W2N902765DE010 E3CD1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R65W2N902765DE010 E3CD1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI ,
E3CD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 857.0 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298683
CATALOG NUMBER: P3AS13R65W2N902765DE010 E3CD1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1298683

CATALOG NUMBER: P3AS13R65W2N902765DE010 E3CD1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93	93	93	93
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87	87	87	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81	81	81	81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75	75	75	75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70	70	70	70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	209435
5°	197116
10°	194608
15°	191170
20°	180499
25°	167526
30°	130223
35°	75329
40°	30343
45°	13986
50°	5424
55°	2103
60°	1842
65°	1816
70°	1795
75°	1779
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13986 cd/sqm



TEST NUMBER: P1298683

CATALOG NUMBER: P3AS13R65W2N902765DE010 E3CD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	9.9
10°-20°	235.2	27.4
20°-30°	307.8	35.9
30°-40°	178.3	20.8
40°-50°	38.2	4.5
50°-60°	6.2	0.7
60°-70°	3.5	0.4
70°-80°	2.0	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	628.1	73.3
0°-40°	806.4	94.1
0°-60°	850.8	99.3
0°-90°	857.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	857.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	955	
5°	896	85
15°	842	235
25°	692	308
35°	281	178
45°	45	38
55°	6	6
65°	4	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1298683
CATALOG NUMBER: P3AS13R65W2N902765DE010 E3CD1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	955.1
2.5°	928.1
5°	895.5
7.5°	882.3
10°	874.0
12.5°	862.2
15°	842.1
17.5°	810.9
20°	773.5
22.5°	738.1
25°	692.4
27.5°	615.5
30°	514.3
32.5°	398.5
35°	281.4
37.5°	178.1
40°	106.0
42.5°	66.5
45°	45.1
47.5°	29.1
50°	15.9
52.5°	7.6
55°	5.5
57.5°	4.9
60°	4.2
62.5°	4.2
65°	3.5
67.5°	2.8
70°	2.8
72.5°	2.1
75°	2.1
77.5°	1.4
80°	1.4
82.5°	0.7
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)