

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298724

Luminaire Tested: P3AS13R65W2N902765DE010 E3DL1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298724
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R65W2N902765DE010 E3DL1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 6500K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 379.0 lumens
Efficiency: N/A
Efficacy: 30.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298724
CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DL1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1298724

CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DL1GPH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63			63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89379
5°	88311
10°	84946
15°	79592
20°	71570
25°	60778
30°	47526
35°	33863
40°	22156
45°	13707
50°	6959
55°	2447
60°	2149
65°	2179
70°	1923
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13707 cd/sqm



TEST NUMBER: P1298724

CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DL1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.7	9.9
10°-20°	97.6	25.7
20°-30°	114.0	30.1
30°-40°	79.7	21.0
40°-50°	35.1	9.3
50°-60°	7.8	2.1
60°-70°	4.0	1.0
70°-80°	2.4	0.6
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	249.2	65.8
0°-40°	328.9	86.8
0°-60°	371.8	98.1
0°-90°	379.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	379.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	408	
5°	401	38
15°	351	98
25°	251	114
35°	126	80
45°	44	35
55°	6	8
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1298724
CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DL1GPH_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	407.6
2.5°	406.1
5°	401.2
7.5°	392.9
10°	381.5
12.5°	367.6
15°	350.6
17.5°	329.8
20°	306.7
22.5°	280.7
25°	251.2
27.5°	220.2
30°	187.7
32.5°	156.4
35°	126.5
37.5°	100.5
40°	77.4
42.5°	58.6
45°	44.2
47.5°	32.5
50°	20.4
52.5°	10.6
55°	6.4
57.5°	5.7
60°	4.9
62.5°	4.5
65°	4.2
67.5°	3.4
70°	3.0
72.5°	2.6
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)