

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298732

Luminaire Tested: P3AS13R65W2N902765DE010 E3DL1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298732
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R65W2N902765DE010 E3DL1LI_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 767.0 lumens
Efficiency: N/A
Efficacy: 62.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298732
CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DL1LI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298732
 CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DL1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 96 | 94 | 93 | 93 | 93 | 93 |
| 2 | 107 | 102 | 98 | 94 | 105 | 100 | 96 | 93 | 97 | 94 | 91 | 94 | 91 | 89 | 91 | 89 | 87 | 85 | 85 | 85 | 85 |
| 3 | 101 | 95 | 89 | 85 | 99 | 93 | 88 | 84 | 90 | 86 | 83 | 88 | 85 | 82 | 86 | 83 | 80 | 79 | 79 | 79 | 79 |
| 4 | 96 | 88 | 82 | 78 | 94 | 87 | 81 | 77 | 85 | 80 | 76 | 83 | 79 | 75 | 81 | 77 | 74 | 73 | 73 | 73 | 73 |
| 5 | 91 | 82 | 76 | 71 | 89 | 81 | 75 | 71 | 79 | 74 | 70 | 77 | 73 | 70 | 76 | 72 | 69 | 68 | 68 | 68 | 68 |
| 6 | 86 | 77 | 70 | 66 | 84 | 76 | 70 | 66 | 74 | 69 | 65 | 73 | 68 | 65 | 72 | 67 | 64 | 63 | 63 | 63 | 63 |
| 7 | 82 | 72 | 66 | 61 | 80 | 71 | 65 | 61 | 70 | 64 | 61 | 69 | 64 | 60 | 67 | 63 | 60 | 58 | 58 | 58 | 58 |
| 8 | 77 | 67 | 61 | 57 | 76 | 67 | 61 | 57 | 66 | 60 | 57 | 65 | 60 | 56 | 64 | 59 | 56 | 55 | 55 | 55 | 55 |
| 9 | 74 | 64 | 57 | 53 | 72 | 63 | 57 | 53 | 62 | 57 | 53 | 61 | 56 | 53 | 60 | 56 | 53 | 51 | 51 | 51 | 51 |
| 10 | 70 | 60 | 54 | 50 | 69 | 59 | 54 | 50 | 59 | 53 | 50 | 58 | 53 | 50 | 57 | 53 | 49 | 48 | 48 | 48 | 48 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 180885 |
| 5° | 178714 |
| 10° | 171918 |
| 15° | 161045 |
| 20° | 144866 |
| 25° | 123007 |
| 30° | 96217 |
| 35° | 68556 |
| 40° | 44855 |
| 45° | 27724 |
| 50° | 14089 |
| 55° | 4970 |
| 60° | 4342 |
| 65° | 4358 |
| 70° | 3911 |
| 75° | 3897 |
| 80° | 3915 |
| 85° | 3774 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27724 cd/sqm



TEST NUMBER: P1298732

CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DL1LI_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 76.2 | 9.9 |
| 10°-20° | 197.4 | 25.7 |
| 20°-30° | 230.8 | 30.1 |
| 30°-40° | 161.3 | 21.0 |
| 40°-50° | 71.0 | 9.3 |
| 50°-60° | 15.8 | 2.1 |
| 60°-70° | 8.0 | 1.0 |
| 70°-80° | 4.9 | 0.6 |
| 80°-90° | 1.7 | 0.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 504.4 | 65.8 |
| 0°-40° | 665.7 | 86.8 |
| 0°-60° | 752.5 | 98.1 |
| 0°-90° | 767.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 767.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 825 | |
| 5° | 812 | 76 |
| 15° | 709 | 197 |
| 25° | 508 | 231 |
| 35° | 256 | 161 |
| 45° | 89 | 71 |
| 55° | 13 | 16 |
| 65° | 8 | 8 |
| 75° | 5 | 5 |
| 85° | 2 | 2 |
| 90° | 0 | |



TEST NUMBER: P1298732
CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DL1LI_3000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 824.9 |
| 2.5° | 821.8 |
| 5° | 811.9 |
| 7.5° | 795.1 |
| 10° | 772.1 |
| 12.5° | 743.8 |
| 15° | 709.4 |
| 17.5° | 667.4 |
| 20° | 620.8 |
| 22.5° | 568.0 |
| 25° | 508.4 |
| 27.5° | 445.7 |
| 30° | 380.0 |
| 32.5° | 316.5 |
| 35° | 256.1 |
| 37.5° | 203.4 |
| 40° | 156.7 |
| 42.5° | 118.5 |
| 45° | 89.4 |
| 47.5° | 65.7 |
| 50° | 41.3 |
| 52.5° | 21.4 |
| 55° | 13.0 |
| 57.5° | 11.5 |
| 60° | 9.9 |
| 62.5° | 9.2 |
| 65° | 8.4 |
| 67.5° | 6.9 |
| 70° | 6.1 |
| 72.5° | 5.4 |
| 75° | 4.6 |
| 77.5° | 3.8 |
| 80° | 3.1 |
| 82.5° | 2.3 |
| 85° | 1.5 |
| 87.5° | 0.8 |
| 90° | 0.0 |

(END OF REPORT)