

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300921

Luminaire Tested: P3AS17R40W2N902765DE010 E3CD1MMS_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300921
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R40W2N902765DE010 E3CD1MMS_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1521.0 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300921
CATALOG NUMBER: P3AS17R40W2N902765DE010 E3CD1MMS_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1300921

CATALOG NUMBER: P3AS17R40W2N902765DE010 E3CD1MMS_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	340.7	22.4
10°-20°	793.4	52.2
20°-30°	344.3	22.6
30°-40°	31.7	2.1
40°-50°	4.5	0.3
50°-60°	2.8	0.2
60°-70°	2.0	0.1
70°-80°	1.2	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1478.4	97.2
0°-40°	1510.1	99.3
0°-60°	1517.4	99.8
0°-90°	1521.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1521.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3652	
5°	3621	341
15°	3005	793
25°	652	344
35°	41	32
45°	4	4
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1300921
CATALOG NUMBER: P3AS17R40W2N902765DE010 E3CD1MMS_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3652.1
2.5°	3647.8
5°	3620.8
7.5°	3563.4
10°	3462.7
12.5°	3292.8
15°	3004.8
17.5°	2527.5
20°	1907.3
22.5°	1238.3
25°	651.6
27.5°	280.4
30°	132.1
32.5°	71.4
35°	41.1
37.5°	24.9
40°	14.1
42.5°	7.6
45°	4.3
47.5°	3.2
50°	3.2
52.5°	3.2
55°	3.2
57.5°	3.2
60°	2.2
62.5°	2.2
65°	2.2
67.5°	2.2
70°	1.1
72.5°	1.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)