

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298780

Luminaire Tested: P3AS13R65W2N902765DE010 E3DLD1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298780
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R65W2N902765DE010 E3DLD1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 602.0 lumens
Efficiency: N/A
Efficacy: 48.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298780
CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DLD1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298780

CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DLD1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107119
5°	105679
10°	102136
15°	96323
20°	88838
25°	80642
30°	71429
35°	60793
40°	48376
45°	34143
50°	19820
55°	10819
60°	10043
65°	9132
70°	8335
75°	7795
80°	6819
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34143 cd/sqm



TEST NUMBER: P1298780
 CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DLD1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.2	7.5
10°-20°	118.7	19.7
20°-30°	152.5	25.3
30°-40°	141.1	23.4
40°-50°	85.2	14.2
50°-60°	29.1	4.8
60°-70°	17.5	2.9
70°-80°	9.9	1.6
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	316.4	52.6
0°-40°	457.6	76.0
0°-60°	571.8	95.0
0°-90°	602.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	602.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	488	
5°	480	45
15°	424	119
25°	333	153
35°	227	141
45°	110	85
55°	28	29
65°	18	17
75°	9	10
85°	2	3
90°	0	



TEST NUMBER: P1298780
CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DLD1WH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	488.5
2.5°	486.3
5°	480.1
7.5°	471.0
10°	458.7
12.5°	443.4
15°	424.3
17.5°	403.7
20°	380.7
22.5°	357.0
25°	333.3
27.5°	308.1
30°	282.1
32.5°	256.1
35°	227.1
37.5°	198.8
40°	169.0
42.5°	139.1
45°	110.1
47.5°	83.3
50°	58.1
52.5°	36.7
55°	28.3
57.5°	25.2
60°	22.9
62.5°	19.9
65°	17.6
67.5°	15.3
70°	13.0
72.5°	11.5
75°	9.2
77.5°	7.6
80°	5.4
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)