

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300935

Luminaire Tested: P3AS17R40W2N902765DE010 E3D1H_3500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300935
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R40W2N902765DE010 E3D1H_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1697.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300935

CATALOG NUMBER: P3AS17R40W2N902765DE010 E3D1H_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1300935

CATALOG NUMBER: P3AS17R40W2N902765DE010 E3D1H_3500K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 368.2 | 21.7 |
| 10°-20° | 871.9 | 51.4 |
| 20°-30° | 395.4 | 23.3 |
| 30°-40° | 51.3 | 3.0 |
| 40°-50° | 8.9 | 0.5 |
| 50°-60° | 1.1 | 0.1 |
| 60°-70° | 0.4 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1635.5 | 96.4 |
| 0°-40° | 1686.7 | 99.4 |
| 0°-60° | 1696.6 | 100.0 |
| 0°-90° | 1697.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1697.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3945 | |
| 5° | 3901 | 368 |
| 15° | 3291 | 872 |
| 25° | 767 | 395 |
| 35° | 72 | 51 |
| 45° | 11 | 9 |
| 55° | 1 | 1 |
| 65° | 1 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1300935

CATALOG NUMBER: P3AS17R40W2N902765DE010 E3D1H_3500K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 3944.7 |
| 1° | 3942.3 |
| 2° | 3936.4 |
| 3° | 3927.5 |
| 4° | 3916.2 |
| 5° | 3901.3 |
| 6° | 3884.1 |
| 7° | 3862.7 |
| 8° | 3836.6 |
| 9° | 3800.9 |
| 10° | 3755.8 |
| 11° | 3702.9 |
| 12° | 3632.2 |
| 13° | 3544.9 |
| 14° | 3430.8 |
| 15° | 3290.6 |
| 16° | 3111.8 |
| 17° | 2908.0 |
| 18° | 2663.3 |
| 19° | 2404.9 |
| 20° | 2122.7 |
| 21° | 1840.5 |
| 22° | 1562.4 |
| 23° | 1285.6 |
| 24° | 1013.5 |
| 25° | 767.0 |
| 26° | 567.9 |
| 27° | 415.9 |
| 28° | 312.5 |
| 29° | 243.0 |
| 30° | 196.0 |
| 31° | 162.2 |
| 32° | 135.5 |
| 32.5° | 123.6 |
| 33° | 111.7 |
| 34° | 90.9 |
| 35° | 72.5 |
| 36° | 57.0 |
| 37° | 45.2 |
| 37.5° | 40.4 |
| 38° | 35.6 |
| 39° | 29.7 |
| 40° | 24.4 |
| 42.5° | 16.0 |
| 45° | 10.7 |



TEST NUMBER: P1300935

CATALOG NUMBER: P3AS17R40W2N902765DE010 E3D1H_3500K

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|-----|
| 47.5° | 6.5 |
| 50° | 3.0 |
| 52.5° | 1.2 |
| 55° | 1.2 |
| 57.5° | 0.6 |
| 60° | 0.6 |
| 62.5° | 0.6 |
| 65° | 0.6 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)