

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298840

Luminaire Tested: P3AS13R70W2N902750DE010 E3CB1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298840
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R70W2N902750DE010 E3CB1MW_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 4000K CCT AND, 90CRI ,
E3CB1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 970.0 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298840
CATALOG NUMBER: P3AS13R70W2N902750DE010 E3CB1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298840

CATALOG NUMBER: P3AS13R70W2N902750DE010 E3CB1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.2	8.1
10°-20°	210.7	21.7
20°-30°	294.3	30.3
30°-40°	272.9	28.1
40°-50°	97.8	10.1
50°-60°	8.3	0.9
60°-70°	4.1	0.4
70°-80°	2.7	0.3
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	583.1	60.1
0°-40°	856.0	88.2
0°-60°	962.2	99.2
0°-90°	970.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	970.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	878	
5°	835	78
15°	750	211
25°	641	294
35°	453	273
45°	117	98
55°	6	8
65°	4	4
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1298840
CATALOG NUMBER: P3AS13R70W2N902750DE010 E3CB1MW_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	878.4
2.5°	865.2
5°	835.0
7.5°	807.1
10°	785.4
12.5°	767.5
15°	749.7
17.5°	728.0
20°	702.4
22.5°	672.9
25°	641.2
27.5°	608.6
30°	569.8
32.5°	520.2
35°	452.8
37.5°	366.7
40°	272.9
42.5°	186.1
45°	117.1
47.5°	65.1
50°	27.9
52.5°	9.3
55°	6.2
57.5°	5.4
60°	5.4
62.5°	4.7
65°	3.9
67.5°	3.9
70°	3.1
72.5°	3.1
75°	2.3
77.5°	2.3
80°	1.6
82.5°	1.6
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)