

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300982

Luminaire Tested: P3AS17R40W2N902765DE010 E3DL1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300982
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R40W2N902765DE010 E3DL1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1391.0 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300982
CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DL1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1300982

CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DL1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94				94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89				89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84				84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80				80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	76				76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72				72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69				69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65				65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	63				63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	60				60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	615499
5°	597621
10°	542319
15°	448039
20°	323195
25°	199899
30°	108219
35°	55921
40°	30428
45°	17025
50°	8563
55°	6384
60°	5745
65°	5552
70°	5386
75°	5083
80°	4546
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17025 cd/sqm



TEST NUMBER: P1300982

CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DL1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.3	18.0
10°-20°	537.4	38.6
20°-30°	383.5	27.6
30°-40°	141.2	10.1
40°-50°	44.5	3.2
50°-60°	15.4	1.1
60°-70°	10.6	0.8
70°-80°	6.3	0.5
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1171.2	84.2
0°-40°	1312.4	94.3
0°-60°	1372.3	98.7
0°-90°	1391.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1391.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2807	
5°	2715	250
15°	1974	537
25°	826	384
35°	209	141
45°	55	44
55°	17	15
65°	11	11
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P1300982
CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DL1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2806.9
2.5°	2785.4
5°	2715.0
7.5°	2598.0
10°	2435.6
12.5°	2229.1
15°	1973.6
17.5°	1687.0
20°	1385.0
22.5°	1087.7
25°	826.2
27.5°	606.5
30°	427.4
32.5°	299.7
35°	208.9
37.5°	148.0
40°	106.3
42.5°	76.4
45°	54.9
47.5°	37.0
50°	25.1
52.5°	17.9
55°	16.7
57.5°	15.5
60°	13.1
62.5°	11.9
65°	10.7
67.5°	9.6
70°	8.4
72.5°	7.2
75°	6.0
77.5°	4.8
80°	3.6
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)