

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301000

Luminaire Tested: P3AS17R40W2N902765DE010 E3DLD1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301000
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R40W2N902765DE010 E3DLD1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 523.0 lumens
Efficiency: N/A
Efficacy: 27.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301000
CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DLD1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1301000

CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DLD1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.8	9.3
10°-20°	121.1	23.2
20°-30°	140.0	26.8
30°-40°	110.3	21.1
40°-50°	56.6	10.8
50°-60°	21.6	4.1
60°-70°	14.3	2.7
70°-80°	7.8	1.5
80°-90°	2.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	309.9	59.3
0°-40°	420.3	80.4
0°-60°	498.5	95.3
0°-90°	523.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	523.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	535	
5°	524	49
15°	435	121
25°	306	140
35°	177	110
45°	73	57
55°	23	22
65°	15	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1301000
CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	535.4
2.5°	532.5
5°	523.7
7.5°	508.5
10°	488.0
12.5°	464.0
15°	434.8
17.5°	404.3
20°	371.6
22.5°	338.2
25°	306.0
27.5°	273.8
30°	242.2
32.5°	210.1
35°	176.7
37.5°	145.7
40°	117.6
42.5°	93.6
45°	73.1
47.5°	53.2
50°	36.3
52.5°	26.3
55°	22.8
57.5°	20.5
60°	18.7
62.5°	16.4
65°	14.6
67.5°	12.3
70°	10.5
72.5°	8.8
75°	7.6
77.5°	5.9
80°	4.1
82.5°	3.5
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)