

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301172

Luminaire Tested: P3AS17R45W2N902750DE010 E3DLP1H\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301172  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R45W2N902750DE010 E3DLP1H\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,  
E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 861.0 lumens  
Efficiency: N/A  
Efficacy: 44.4 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301172  
CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLP1H\_3000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1301172

CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLP1H\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.4	12.2
10°-20°	244.8	28.4
20°-30°	243.0	28.2
30°-40°	156.5	18.2
40°-50°	60.3	7.0
50°-60°	24.5	2.8
60°-70°	15.5	1.8
70°-80°	8.3	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	593.3	68.9
0°-40°	749.8	87.1
0°-60°	834.6	96.9
0°-90°	861.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	861.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1170	
5°	1138	105
15°	886	245
25°	531	243
35°	249	157
45°	73	60
55°	27	25
65°	16	15
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1301172  
CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLP1H\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1169.5
2.5°	1163.6
5°	1138.5
7.5°	1095.6
10°	1038.3
12.5°	966.7
15°	885.5
17.5°	797.2
20°	707.7
22.5°	617.0
25°	531.1
27.5°	449.9
30°	374.7
32.5°	309.1
35°	249.4
37.5°	195.7
40°	145.6
42.5°	105.0
45°	72.8
47.5°	48.9
50°	35.8
52.5°	29.8
55°	27.4
57.5°	23.9
60°	21.5
62.5°	17.9
65°	15.5
67.5°	13.1
70°	10.7
72.5°	9.5
75°	8.4
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)