

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299038

Luminaire Tested: P3AS13R70W2N902765DE010 E3DL1MW_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R70W2N902765DE010 E3DL1MW_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3500K CCT AND, 90CRI ,
E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 781.0 lumens
Efficiency: N/A
Efficacy: 63.5 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299038
CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DL1MW_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1299038

CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DL1MW_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151194
5°	149372
10°	145065
15°	138911
20°	130141
25°	118217
30°	102117
35°	81378
40°	59282
45°	38950
50°	18251
55°	5620
60°	5438
65°	5241
70°	5001
75°	5253
80°	4925
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 38950 cd/sqm



TEST NUMBER: P1299038

CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DL1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.9	8.2
10°-20°	171.3	21.9
20°-30°	222.6	28.5
30°-40°	188.9	24.2
40°-50°	97.4	12.5
50°-60°	18.8	2.4
60°-70°	10.2	1.3
70°-80°	6.3	0.8
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	457.8	58.6
0°-40°	646.6	82.8
0°-60°	762.8	97.7
0°-90°	781.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	781.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	690	
5°	679	64
15°	612	171
25°	489	223
35°	304	189
45°	126	97
55°	15	19
65°	10	10
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1299038
CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DL1MW_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	689.5
2.5°	687.2
5°	678.6
7.5°	666.2
10°	651.5
12.5°	632.9
15°	611.9
17.5°	586.3
20°	557.7
22.5°	525.1
25°	488.6
27.5°	447.5
30°	403.3
32.5°	354.4
35°	304.0
37.5°	254.4
40°	207.1
42.5°	162.9
45°	125.6
47.5°	92.3
50°	53.5
52.5°	23.3
55°	14.7
57.5°	14.0
60°	12.4
62.5°	11.6
65°	10.1
67.5°	9.3
70°	7.8
72.5°	7.0
75°	6.2
77.5°	4.7
80°	3.9
82.5°	2.3
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)