

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299180

Luminaire Tested: P3AS17R15W2N902750DE010 E3DL1WH\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299180  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R15W2N902750DE010 E3DL1WH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 90CRI ,  
E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 745.9 lumens  
Efficiency: N/A  
Efficacy: 38.5 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299180  
CATALOG NUMBER: P3AS17R15W2N902750DE010 E3DL1WH\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299180  
 CATALOG NUMBER: P3AS17R15W2N902750DE010 E3DL1WH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	321685
5°	297314
10°	237381
15°	179297
20°	136535
25°	104062
30°	74543
35°	48640
40°	29827
45°	18017
50°	11974
55°	9252
60°	7982
65°	6901
70°	6219
75°	6185
80°	4546
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18017 cd/sqm



TEST NUMBER: P1299180

CATALOG NUMBER: P3AS17R15W2N902750DE010 E3DL1WH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	119.7	16.0
10°-20°	220.8	29.6
20°-30°	196.5	26.3
30°-40°	116.3	15.6
40°-50°	47.7	6.4
50°-60°	22.4	3.0
60°-70°	13.6	1.8
70°-80°	7.2	1.0
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	537.0	72.0
0°-40°	653.3	87.6
0°-60°	723.4	97.0
0°-90°	745.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	745.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1467	
5°	1351	120
15°	790	221
25°	430	197
35°	182	116
45°	58	48
55°	24	22
65°	13	14
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P1299180  
CATALOG NUMBER: P3AS17R15W2N902750DE010 E3DL1WH\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1467.0
1°	1463.4
2°	1452.5
3°	1430.7
4°	1394.3
5°	1350.7
6°	1303.5
7°	1247.8
8°	1189.6
9°	1130.3
10°	1066.1
12.5°	919.5
15°	789.8
17.5°	678.4
20°	585.1
22.5°	502.7
25°	430.1
27.5°	359.8
30°	294.4
32.5°	235.0
35°	181.7
37.5°	139.3
40°	104.2
42.5°	77.5
45°	58.1
47.5°	44.8
50°	35.1
52.5°	29.1
55°	24.2
57.5°	20.6
60°	18.2
62.5°	15.7
65°	13.3
67.5°	12.1
70°	9.7
72.5°	8.5
75°	7.3
77.5°	4.8
80°	3.6
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)