

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299208

Luminaire Tested: P3AS17R15W2N902750DE010 E3DLD1WH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299208  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R15W2N902750DE010 E3DLD1WH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 942.0 lumens  
Efficiency: N/A  
Efficacy: 48.6 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299208  
CATALOG NUMBER: P3AS17R15W2N902750DE010 E3DLD1WH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299208  
 CATALOG NUMBER: P3AS17R15W2N902750DE010 E3DLD1WH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65			65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56			56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	237613
5°	231168
10°	211241
15°	185041
20°	158727
25°	132540
30°	106067
35°	79531
40°	57737
45°	37740
50°	23607
55°	15980
60°	14122
65°	13023
70°	12246
75°	11099
80°	10607
85°	9057

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 37740 cd/sqm



TEST NUMBER: P1299208  
 CATALOG NUMBER: P3AS17R15W2N902750DE010 E3DLD1WH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.9	10.3
10°-20°	227.1	24.1
20°-30°	250.2	26.6
30°-40°	187.4	19.9
40°-50°	97.1	10.3
50°-60°	40.3	4.3
60°-70°	24.9	2.6
70°-80°	14.0	1.5
80°-90°	4.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.2	61.0
0°-40°	761.6	80.8
0°-60°	899.0	95.4
0°-90°	942.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	942.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1084	
5°	1050	97
15°	815	227
25°	548	250
35°	297	187
45°	122	97
55°	42	40
65°	25	25
75°	13	14
85°	4	4
90°	0	



TEST NUMBER: P1299208  
CATALOG NUMBER: P3AS17R15W2N902750DE010 E3DLD1WH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1083.6
1°	1084.8
2°	1081.2
3°	1074.0
4°	1063.3
5°	1050.2
6°	1033.5
7°	1015.6
8°	994.1
9°	971.4
10°	948.7
12.5°	883.1
15°	815.1
17.5°	747.0
20°	680.2
22.5°	612.2
25°	547.8
27.5°	483.3
30°	418.9
32.5°	355.6
35°	297.1
37.5°	247.0
40°	201.7
42.5°	159.9
45°	121.7
47.5°	91.9
50°	69.2
52.5°	51.3
55°	41.8
57.5°	37.0
60°	32.2
62.5°	28.6
65°	25.1
67.5°	21.5
70°	19.1
72.5°	15.5
75°	13.1
77.5°	10.7
80°	8.4
82.5°	6.0
85°	3.6
87.5°	1.2
90°	0.0

(END OF REPORT)