

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301310

Luminaire Tested: P3AS17R45W2N902765DE010 E3DLP1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301310
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R45W2N902765DE010 E3DLP1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 383.0 lumens
Efficiency: N/A
Efficacy: 19.7 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301310
CATALOG NUMBER: P3AS17R45W2N902765DE010 E3DLP1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1301310
 CATALOG NUMBER: P3AS17R45W2N902765DE010 E3DLP1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20						
RC	80				70				50				30				10					0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																							
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93					
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86					
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79					
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74					
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69					
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64					
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60					
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56					
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53					
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50					

AVERAGE LUMINANCE (cd/sqm):

0°	
0°	114070
5°	111468
10°	102848
15°	89422
20°	73460
25°	57148
30°	42209
35°	29714
40°	18549
45°	10048
50°	5424
55°	4664
60°	4210
65°	3580
70°	3077
75°	3135
80°	2652
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10048 cd/sqm



TEST NUMBER: P1301310
 CATALOG NUMBER: P3AS17R45W2N902765DE010 E3DLP1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.9	12.2
10°-20°	108.9	28.4
20°-30°	108.1	28.2
30°-40°	69.6	18.2
40°-50°	26.8	7.0
50°-60°	10.9	2.8
60°-70°	6.9	1.8
70°-80°	3.7	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	263.9	68.9
0°-40°	333.5	87.1
0°-60°	371.3	96.9
0°-90°	383.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	383.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	520	
5°	506	47
15°	394	109
25°	236	108
35°	111	70
45°	32	27
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1301310
CATALOG NUMBER: P3AS17R45W2N902765DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	520.2
2.5°	517.6
5°	506.4
7.5°	487.3
10°	461.9
12.5°	430.0
15°	393.9
17.5°	354.6
20°	314.8
22.5°	274.5
25°	236.2
27.5°	200.1
30°	166.7
32.5°	137.5
35°	111.0
37.5°	87.1
40°	64.8
42.5°	46.7
45°	32.4
47.5°	21.8
50°	15.9
52.5°	13.3
55°	12.2
57.5°	10.6
60°	9.6
62.5°	8.0
65°	6.9
67.5°	5.8
70°	4.8
72.5°	4.2
75°	3.7
77.5°	2.7
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)