

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299243

Luminaire Tested: P3AS17R15W2N902750DE010 E3DLP1WMH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299243  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R15W2N902750DE010 E3DLP1WMH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,  
E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 735.0 lumens  
Efficiency: N/A  
Efficacy: 37.9 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299243  
CATALOG NUMBER: P3AS17R15W2N902750DE010 E3DLP1WMH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299243

CATALOG NUMBER: P3AS17R15W2N902750DE010 E3DLP1WMH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	316948
5°	292933
10°	233863
15°	176664
20°	134528
25°	102514
30°	73429
35°	47917
40°	29369
45°	17769
50°	11803
55°	9137
60°	7850
65°	6797
70°	6091
75°	6100
80°	4546
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17769 cd/sqm



TEST NUMBER: P1299243

CATALOG NUMBER: P3AS17R15W2N902750DE010 E3DLP1WMH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.9	16.0
10°-20°	217.5	29.6
20°-30°	193.6	26.3
30°-40°	114.6	15.6
40°-50°	47.0	6.4
50°-60°	22.1	3.0
60°-70°	13.4	1.8
70°-80°	7.1	1.0
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.0	72.0
0°-40°	643.6	87.6
0°-60°	712.7	97.0
0°-90°	735.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	735.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1445	
5°	1331	118
15°	778	218
25°	424	194
35°	179	115
45°	57	47
55°	24	22
65°	13	13
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P1299243

CATALOG NUMBER: P3AS17R15W2N902750DE010 E3DLP1WMH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1445.4
1°	1441.8
2°	1431.1
3°	1409.6
4°	1373.8
5°	1330.8
6°	1284.3
7°	1229.4
8°	1172.1
9°	1113.6
10°	1050.3
12.5°	905.9
15°	778.2
17.5°	668.4
20°	576.5
22.5°	495.3
25°	423.7
27.5°	354.5
30°	290.0
32.5°	231.6
35°	179.0
37.5°	137.3
40°	102.6
42.5°	76.4
45°	57.3
47.5°	44.2
50°	34.6
52.5°	28.6
55°	23.9
57.5°	20.3
60°	17.9
62.5°	15.5
65°	13.1
67.5°	11.9
70°	9.5
72.5°	8.4
75°	7.2
77.5°	4.8
80°	3.6
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)