

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301387

Luminaire Tested: P3AS17R50W2N902750DE010 E3D1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301387
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R50W2N902750DE010 E3D1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,
E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1635.0 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301387
CATALOG NUMBER: P3AS17R50W2N902750DE010 E3D1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1301387

CATALOG NUMBER: P3AS17R50W2N902750DE010 E3D1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	66	65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	569428
5°	559233
10°	536953
15°	492398
20°	434178
25°	332801
30°	180939
35°	58223
40°	13683
45°	1861
50°	1637
55°	1835
60°	1579
65°	1868
70°	1539
75°	2033
80°	1515
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 85°
 Luminance: 3019 cd/sqm



TEST NUMBER: P1301387

CATALOG NUMBER: P3AS17R50W2N902750DE010 E3D1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.4	14.6
10°-20°	602.9	36.9
20°-30°	603.8	36.9
30°-40°	169.8	10.4
40°-50°	10.3	0.6
50°-60°	3.9	0.2
60°-70°	3.1	0.2
70°-80°	2.1	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1445.1	88.4
0°-40°	1614.9	98.8
0°-60°	1629.1	99.6
0°-90°	1635.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1635.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2597	
5°	2541	238
15°	2169	603
25°	1376	604
35°	218	170
45°	6	10
55°	5	4
65°	4	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1301387
CATALOG NUMBER: P3AS17R50W2N902750DE010 E3D1MW_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2596.8
2.5°	2583.6
5°	2540.6
7.5°	2482.0
10°	2411.5
12.5°	2305.2
15°	2169.0
17.5°	2012.4
20°	1860.6
22.5°	1671.8
25°	1375.5
27.5°	1024.1
30°	714.6
32.5°	431.4
35°	217.5
37.5°	102.8
40°	47.8
42.5°	17.9
45°	6.0
47.5°	4.8
50°	4.8
52.5°	4.8
55°	4.8
57.5°	3.6
60°	3.6
62.5°	3.6
65°	3.6
67.5°	2.4
70°	2.4
72.5°	2.4
75°	2.4
77.5°	1.2
80°	1.2
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0

(END OF REPORT)