

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301432

Luminaire Tested: P3AS17R50W2N902750DE010 E3DLD1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301432
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R50W2N902750DE010 E3DLD1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 513.0 lumens
Efficiency: N/A
Efficacy: 26.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301432
CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DLD1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1301432
 CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DLD1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93		91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84		83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77		75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70		69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64		63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59		58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55		53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51		50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48		46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45		43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104246
5°	102707
10°	98172
15°	90920
20°	81697
25°	71811
30°	61073
35°	49523
40°	37213
45°	23971
50°	11394
55°	8946
60°	8464
65°	7887
70°	7117
75°	6439
80°	5935
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23971 cd/sqm



TEST NUMBER: P1301432

CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DLD1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.7	8.5
10°-20°	111.7	21.8
20°-30°	135.6	26.4
30°-40°	115.0	22.4
40°-50°	59.8	11.6
50°-60°	21.6	4.2
60°-70°	14.9	2.9
70°-80°	8.1	1.6
80°-90°	2.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	291.1	56.7
0°-40°	406.1	79.2
0°-60°	487.4	95.0
0°-90°	513.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	513.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	475	
5°	467	44
15°	400	112
25°	297	136
35°	185	115
45°	77	60
55°	23	22
65°	15	15
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1301432
CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	475.4
2.5°	473.7
5°	466.6
7.5°	456.1
10°	440.9
12.5°	421.6
15°	400.5
17.5°	376.5
20°	350.1
22.5°	323.2
25°	296.8
27.5°	269.3
30°	241.2
32.5°	213.1
35°	185.0
37.5°	157.5
40°	130.0
42.5°	103.6
45°	77.3
47.5°	51.5
50°	33.4
52.5°	25.8
55°	23.4
57.5°	21.1
60°	19.3
62.5°	17.0
65°	15.2
67.5°	12.9
70°	11.1
72.5°	9.4
75°	7.6
77.5°	5.9
80°	4.7
82.5°	3.5
85°	2.3
87.5°	1.2
90°	0.0

(END OF REPORT)