

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301433

Luminaire Tested: P3AS17R50W2N902750DE010 E3DLD1GPH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301433  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R50W2N902750DE010 E3DLD1GPH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3500K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 520.0 lumens  
Efficiency: N/A  
Efficacy: 26.8 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301433  
CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DLD1GPH\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1301433

CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DLD1GPH\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	105671
5°	104116
10°	99508
15°	92146
20°	82817
25°	72803
30°	61908
35°	50192
40°	37728
45°	24282
50°	11531
55°	9061
60°	8596
65°	7990
70°	7245
75°	6524
80°	5935
85°	6038

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24282 cd/sqm



TEST NUMBER: P1301433

CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DLD1GPH\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.3	8.5
10°-20°	113.2	21.8
20°-30°	137.5	26.4
30°-40°	116.6	22.4
40°-50°	60.6	11.6
50°-60°	21.9	4.2
60°-70°	15.1	2.9
70°-80°	8.2	1.6
80°-90°	2.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	295.0	56.7
0°-40°	411.6	79.2
0°-60°	494.0	95.0
0°-90°	520.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	520.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	482	
5°	473	44
15°	406	113
25°	301	138
35°	188	117
45°	78	61
55°	24	22
65°	15	15
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1301433  
CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DLD1GPH\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	481.9
2.5°	480.1
5°	473.0
7.5°	462.3
10°	446.9
12.5°	427.3
15°	405.9
17.5°	381.6
20°	354.9
22.5°	327.6
25°	300.9
27.5°	273.0
30°	244.5
32.5°	216.0
35°	187.5
37.5°	159.6
40°	131.8
42.5°	105.0
45°	78.3
47.5°	52.2
50°	33.8
52.5°	26.1
55°	23.7
57.5°	21.4
60°	19.6
62.5°	17.2
65°	15.4
67.5°	13.1
70°	11.3
72.5°	9.5
75°	7.7
77.5°	5.9
80°	4.7
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)