

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299331

Luminaire Tested: P3AS17R15W2N902765DE010 E3DL1GPH\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299331  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R15W2N902765DE010 E3DL1GPH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 617.0 lumens  
Efficiency: N/A  
Efficacy: 31.8 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299331  
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1GPH\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299331

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1GPH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	93	93	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	88	88	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	85	85	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	81	81	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	78	78	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	75	75	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	73	73	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	70	70	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	68	68	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	527085
5°	467861
10°	324910
15°	192146
20°	109443
25°	62568
30°	34613
35°	18444
40°	10219
45°	5520
50°	3446
55°	2714
60°	2324
65°	2179
70°	1923
75°	2033
80°	1515
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5520 cd/sqm



TEST NUMBER: P1299331

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1GPH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	180.7	29.3
10°-20°	238.5	38.7
20°-30°	122.8	19.9
30°-40°	46.1	7.5
40°-50°	15.1	2.4
50°-60°	6.5	1.0
60°-70°	4.1	0.7
70°-80°	2.5	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	542.1	87.9
0°-40°	588.2	95.3
0°-60°	609.8	98.8
0°-90°	617.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	617.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2404	
5°	2126	181
15°	846	239
25°	259	123
35°	69	46
45°	18	15
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1299331  
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1GPH\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2403.7
1°	2398.9
2°	2367.4
3°	2307.4
4°	2228.3
5°	2125.5
6°	2009.0
7°	1881.2
8°	1739.2
9°	1598.9
10°	1459.2
12.5°	1122.8
15°	846.4
17.5°	633.6
20°	469.0
22.5°	350.1
25°	258.6
27.5°	188.4
30°	136.7
32.5°	96.9
35°	68.9
37.5°	49.3
40°	35.7
42.5°	25.6
45°	17.8
47.5°	13.1
50°	10.1
52.5°	8.3
55°	7.1
57.5°	5.9
60°	5.3
62.5°	4.8
65°	4.2
67.5°	3.6
70°	3.0
72.5°	3.0
75°	2.4
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)