

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299334

Luminaire Tested: P3AS17R15W2N902765DE010 E3DL1H\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299334  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R15W2N902765DE010 E3DL1H\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI ,  
E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1124.0 lumens  
Efficiency: N/A  
Efficacy: 57.9 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299334  
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1H\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299334

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1H\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	960186
5°	852320
10°	591906
15°	350036
20°	199354
25°	113958
30°	63048
35°	33622
40°	18606
45°	10079
50°	6277
55°	4970
60°	4254
65°	3943
70°	3462
75°	3643
80°	2778
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10079 cd/sqm



TEST NUMBER: P1299334

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1H\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	329.3	29.3
10°-20°	434.6	38.7
20°-30°	223.7	19.9
30°-40°	84.0	7.5
40°-50°	27.5	2.4
50°-60°	11.8	1.1
60°-70°	7.5	0.7
70°-80°	4.4	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	987.6	87.9
0°-40°	1071.6	95.3
0°-60°	1110.9	98.8
0°-90°	1124.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1124.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4379	
5°	3872	329
15°	1542	435
25°	471	224
35°	126	84
45°	32	28
55°	13	12
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1299334  
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1H\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4378.8
1°	4370.2
2°	4312.8
3°	4203.4
4°	4059.4
5°	3872.1
6°	3659.8
7°	3427.0
8°	3168.3
9°	2912.7
10°	2658.3
12.5°	2045.4
15°	1541.9
17.5°	1154.3
20°	854.3
22.5°	637.8
25°	471.0
27.5°	343.2
30°	249.0
32.5°	176.5
35°	125.6
37.5°	89.9
40°	65.0
42.5°	46.6
45°	32.5
47.5°	23.8
50°	18.4
52.5°	15.2
55°	13.0
57.5°	10.8
60°	9.7
62.5°	8.7
65°	7.6
67.5°	6.5
70°	5.4
72.5°	5.4
75°	4.3
77.5°	3.2
80°	2.2
82.5°	2.2
85°	1.1
87.5°	0.0
90°	0.0

(END OF REPORT)