

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299341

Luminaire Tested: P3AS17R15W2N902765DE010 E3DL1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299341
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R15W2N902765DE010 E3DL1LI_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1239.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299341
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1LI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299341
 CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | | 0 |
| RCR | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | | 100 |
| 1 | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | | 95 |
| 2 | 110 | 106 | 103 | 100 | 108 | 104 | 101 | 99 | 101 | 99 | 97 | 98 | 96 | 95 | 96 | 94 | 93 | | 91 |
| 3 | 106 | 101 | 97 | 93 | 104 | 99 | 96 | 93 | 97 | 94 | 91 | 94 | 92 | 90 | 92 | 90 | 88 | | 87 |
| 4 | 102 | 96 | 92 | 88 | 100 | 95 | 91 | 88 | 93 | 89 | 87 | 91 | 88 | 86 | 89 | 87 | 85 | | 83 |
| 5 | 98 | 92 | 87 | 84 | 97 | 91 | 87 | 83 | 89 | 85 | 83 | 88 | 84 | 82 | 86 | 83 | 81 | | 80 |
| 6 | 95 | 88 | 83 | 80 | 94 | 87 | 83 | 80 | 86 | 82 | 79 | 85 | 81 | 79 | 83 | 80 | 78 | | 77 |
| 7 | 92 | 85 | 80 | 77 | 91 | 84 | 80 | 76 | 83 | 79 | 76 | 82 | 78 | 76 | 81 | 78 | 75 | | 74 |
| 8 | 89 | 81 | 77 | 74 | 88 | 81 | 77 | 73 | 80 | 76 | 73 | 79 | 75 | 73 | 78 | 75 | 73 | | 72 |
| 9 | 86 | 79 | 74 | 71 | 85 | 78 | 74 | 71 | 77 | 73 | 71 | 77 | 73 | 70 | 76 | 73 | 70 | | 69 |
| 10 | 84 | 76 | 71 | 68 | 83 | 76 | 71 | 68 | 75 | 71 | 68 | 74 | 71 | 68 | 74 | 70 | 68 | | 67 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1058424 |
| 5° | 939509 |
| 10° | 652448 |
| 15° | 385859 |
| 20° | 219749 |
| 25° | 125620 |
| 30° | 69504 |
| 35° | 37075 |
| 40° | 20496 |
| 45° | 11102 |
| 50° | 6925 |
| 55° | 5467 |
| 60° | 4693 |
| 65° | 4358 |
| 70° | 3847 |
| 75° | 4067 |
| 80° | 3031 |
| 85° | 3019 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11102 cd/sqm



TEST NUMBER: P1299341

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1LI_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 363.0 | 29.3 |
| 10°-20° | 479.0 | 38.7 |
| 20°-30° | 246.6 | 19.9 |
| 30°-40° | 92.6 | 7.5 |
| 40°-50° | 30.3 | 2.4 |
| 50°-60° | 13.0 | 1.1 |
| 60°-70° | 8.3 | 0.7 |
| 70°-80° | 4.9 | 0.4 |
| 80°-90° | 1.3 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1088.6 | 87.9 |
| 0°-40° | 1181.2 | 95.3 |
| 0°-60° | 1224.6 | 98.8 |
| 0°-90° | 1239.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1239.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4827 | |
| 5° | 4268 | 363 |
| 15° | 1700 | 479 |
| 25° | 519 | 247 |
| 35° | 138 | 93 |
| 45° | 36 | 30 |
| 55° | 14 | 13 |
| 65° | 8 | 8 |
| 75° | 5 | 5 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P1299341
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1LI_3000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 4826.8 |
| 1° | 4817.3 |
| 2° | 4754.0 |
| 3° | 4633.5 |
| 4° | 4474.7 |
| 5° | 4268.2 |
| 6° | 4034.3 |
| 7° | 3777.7 |
| 8° | 3492.4 |
| 9° | 3210.7 |
| 10° | 2930.2 |
| 12.5° | 2254.7 |
| 15° | 1699.7 |
| 17.5° | 1272.4 |
| 20° | 941.7 |
| 22.5° | 703.0 |
| 25° | 519.2 |
| 27.5° | 378.4 |
| 30° | 274.5 |
| 32.5° | 194.6 |
| 35° | 138.5 |
| 37.5° | 99.1 |
| 40° | 71.6 |
| 42.5° | 51.3 |
| 45° | 35.8 |
| 47.5° | 26.3 |
| 50° | 20.3 |
| 52.5° | 16.7 |
| 55° | 14.3 |
| 57.5° | 11.9 |
| 60° | 10.7 |
| 62.5° | 9.5 |
| 65° | 8.4 |
| 67.5° | 7.2 |
| 70° | 6.0 |
| 72.5° | 6.0 |
| 75° | 4.8 |
| 77.5° | 3.6 |
| 80° | 2.4 |
| 82.5° | 2.4 |
| 85° | 1.2 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)