

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299364

Luminaire Tested: P3AS17R15W2N902765DE010 E3DLD1GPH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299364  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R15W2N902765DE010 E3DLD1GPH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 419.0 lumens  
Efficiency: N/A  
Efficacy: 21.6 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299364  
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1GPH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299364

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1GPH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91				91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83				83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76				76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70				70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65				65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60				60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56				56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52				52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49				49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	105693
5°	102817
10°	93964
15°	82293
20°	70613
25°	58939
30°	47172
35°	35389
40°	25677
45°	16777
50°	10507
55°	7111
60°	6271
65°	5759
70°	5450
75°	4914
80°	4672
85°	4026

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16777 cd/sqm



TEST NUMBER: P1299364

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1GPH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	43.1	10.3
10°-20°	101.0	24.1
20°-30°	111.3	26.6
30°-40°	83.4	19.9
40°-50°	43.2	10.3
50°-60°	17.9	4.3
60°-70°	11.1	2.6
70°-80°	6.2	1.5
80°-90°	1.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.4	61.0
0°-40°	338.8	80.9
0°-60°	399.9	95.4
0°-90°	419.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	419.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	482	
5°	467	43
15°	362	101
25°	244	111
35°	132	83
45°	54	43
55°	19	18
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1299364  
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1GPH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	482.0
1°	482.5
2°	480.9
3°	477.7
4°	472.9
5°	467.1
6°	459.7
7°	451.7
8°	442.2
9°	432.1
10°	422.0
12.5°	392.8
15°	362.5
17.5°	332.3
20°	302.6
22.5°	272.3
25°	243.6
27.5°	215.0
30°	186.3
32.5°	158.2
35°	132.2
37.5°	109.9
40°	89.7
42.5°	71.1
45°	54.1
47.5°	40.9
50°	30.8
52.5°	22.8
55°	18.6
57.5°	16.5
60°	14.3
62.5°	12.7
65°	11.1
67.5°	9.6
70°	8.5
72.5°	6.9
75°	5.8
77.5°	4.8
80°	3.7
82.5°	2.7
85°	1.6
87.5°	0.5
90°	0.0

(END OF REPORT)