

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299371

Luminaire Tested: P3AS17R15W2N902765DE010 E3DLD1H_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299371
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R15W2N902765DE010 E3DLD1H_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 942.0 lumens
Efficiency: N/A
Efficacy: 48.6 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299371
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1H_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299371

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1H_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.9	10.3
10°-20°	227.1	24.1
20°-30°	250.2	26.6
30°-40°	187.4	19.9
40°-50°	97.1	10.3
50°-60°	40.3	4.3
60°-70°	24.9	2.6
70°-80°	14.0	1.5
80°-90°	4.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.2	61.0
0°-40°	761.6	80.8
0°-60°	899.0	95.4
0°-90°	942.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	942.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1084	
5°	1050	97
15°	815	227
25°	548	250
35°	297	187
45°	122	97
55°	42	40
65°	25	25
75°	13	14
85°	4	4
90°	0	



TEST NUMBER: P1299371
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1H_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1083.6
1°	1084.8
2°	1081.2
3°	1074.0
4°	1063.3
5°	1050.2
6°	1033.5
7°	1015.6
8°	994.1
9°	971.4
10°	948.7
12.5°	883.1
15°	815.1
17.5°	747.0
20°	680.2
22.5°	612.2
25°	547.8
27.5°	483.3
30°	418.9
32.5°	355.6
35°	297.1
37.5°	247.0
40°	201.7
42.5°	159.9
45°	121.7
47.5°	91.9
50°	69.2
52.5°	51.3
55°	41.8
57.5°	37.0
60°	32.2
62.5°	28.6
65°	25.1
67.5°	21.5
70°	19.1
72.5°	15.5
75°	13.1
77.5°	10.7
80°	8.4
82.5°	6.0
85°	3.6
87.5°	1.2
90°	0.0

(END OF REPORT)