

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299375

Luminaire Tested: P3AS17R15W2N902765DE010 E3DLD1H_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299375
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R15W2N902765DE010 E3DLD1H_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 6500K CCT AND, 90CRI ,
E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 951.0 lumens
Efficiency: N/A
Efficacy: 49.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299375
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1H_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1299375

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1H_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.8	10.3
10°-20°	229.3	24.1
20°-30°	252.6	26.6
30°-40°	189.2	19.9
40°-50°	98.1	10.3
50°-60°	40.6	4.3
60°-70°	25.2	2.6
70°-80°	14.1	1.5
80°-90°	4.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	579.7	61.0
0°-40°	768.9	80.9
0°-60°	907.6	95.4
0°-90°	951.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	951.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1094	
5°	1060	98
15°	823	229
25°	553	253
35°	300	189
45°	123	98
55°	42	41
65°	25	25
75°	13	14
85°	4	4
90°	0	



TEST NUMBER: P1299375
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1H_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1093.9
1°	1095.1
2°	1091.5
3°	1084.3
4°	1073.4
5°	1060.2
6°	1043.3
7°	1025.3
8°	1003.6
9°	980.7
10°	957.8
12.5°	891.5
15°	822.9
17.5°	754.2
20°	686.7
22.5°	618.0
25°	553.0
27.5°	487.9
30°	422.9
32.5°	359.0
35°	300.0
37.5°	249.4
40°	203.6
42.5°	161.4
45°	122.9
47.5°	92.8
50°	69.9
52.5°	51.8
55°	42.2
57.5°	37.3
60°	32.5
62.5°	28.9
65°	25.3
67.5°	21.7
70°	19.3
72.5°	15.7
75°	13.3
77.5°	10.8
80°	8.4
82.5°	6.0
85°	3.6
87.5°	1.2
90°	0.0

(END OF REPORT)