

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301621

Luminaire Tested: P3AS17R50W2N902765DE010 E3DLD1WH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301621  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R50W2N902765DE010 E3DLD1WH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 5000K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1056.0 lumens  
Efficiency: N/A  
Efficacy: 54.4 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301621  
CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLD1WH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1301621

CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLD1WH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	214610
5°	211446
10°	202067
15°	187152
20°	168178
25°	147855
30°	125741
35°	101964
40°	76601
45°	49338
50°	23436
55°	18427
60°	17455
65°	16240
70°	14682
75°	13302
80°	12123
85°	12077

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 49338 cd/sqm



TEST NUMBER: P1301621

CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLD1WH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.0	8.5
10°-20°	229.8	21.8
20°-30°	279.3	26.4
30°-40°	236.8	22.4
40°-50°	123.0	11.7
50°-60°	44.4	4.2
60°-70°	30.7	2.9
70°-80°	16.7	1.6
80°-90°	5.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	599.1	56.7
0°-40°	836.0	79.2
0°-60°	1003.4	95.0
0°-90°	1056.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1056.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	979	
5°	961	90
15°	824	230
25°	611	279
35°	381	237
45°	159	123
55°	48	44
65°	31	31
75°	16	17
85°	5	5
90°	0	



TEST NUMBER: P1301621  
CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLD1WH\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	978.7
2.5°	975.0
5°	960.6
7.5°	938.9
10°	907.5
12.5°	867.8
15°	824.4
17.5°	775.0
20°	720.7
22.5°	665.3
25°	611.1
27.5°	554.4
30°	496.6
32.5°	438.7
35°	380.9
37.5°	324.2
40°	267.6
42.5°	213.3
45°	159.1
47.5°	106.1
50°	68.7
52.5°	53.0
55°	48.2
57.5°	43.4
60°	39.8
62.5°	35.0
65°	31.3
67.5°	26.5
70°	22.9
72.5°	19.3
75°	15.7
77.5°	12.1
80°	9.6
82.5°	7.2
85°	4.8
87.5°	2.4
90°	0.0

(END OF REPORT)