

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301633

Luminaire Tested: P3AS17R50W2N902765DE010 E3DLP1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R50W2N902765DE010 E3DLP1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 5000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 436.1 lumens
Efficiency: N/A
Efficacy: 22.5 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301633
CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLP1GPH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1301633

CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLP1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.9	11.9
10°-20°	122.1	28.0
20°-30°	124.9	28.6
30°-40°	79.2	18.2
40°-50°	31.5	7.2
50°-60°	12.8	2.9
60°-70°	8.2	1.9
70°-80°	4.2	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	298.9	68.5
0°-40°	378.1	86.7
0°-60°	422.4	96.9
0°-90°	436.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	436.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	578	
5°	561	52
15°	441	122
25°	274	125
35°	125	79
45°	38	32
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1301633
CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLP1GPH_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	578.3
2.5°	574.2
5°	560.6
7.5°	539.3
10°	511.0
12.5°	477.4
15°	440.8
17.5°	400.7
20°	358.8
22.5°	316.9
25°	274.4
27.5°	231.9
30°	192.4
32.5°	157.0
35°	125.1
37.5°	98.0
40°	74.4
42.5°	54.9
45°	38.4
47.5°	26.0
50°	18.9
52.5°	15.9
55°	14.2
57.5°	12.4
60°	10.6
62.5°	9.4
65°	8.3
67.5°	7.1
70°	5.9
72.5°	4.7
75°	4.1
77.5°	3.0
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)