

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299381

Luminaire Tested: P3AS17R15W2N902765DE010 E3DLD1LI_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299381
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R15W2N902765DE010 E3DLD1LI_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 6500K CCT AND, 90CRI ,
E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 951.0 lumens
Efficiency: N/A
Efficacy: 49.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299381
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1LI_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1299381

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1LI_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99 | 99 | 98 | 96 | 96 | 95 | 93 | 91 | | | |
| 2 | 106 | 100 | 96 | 92 | 104 | 99 | 95 | 91 | 95 | 92 | 89 | 92 | 90 | 87 | 90 | 87 | 85 | 83 | | | |
| 3 | 100 | 93 | 87 | 83 | 98 | 91 | 86 | 82 | 89 | 84 | 81 | 86 | 82 | 79 | 84 | 81 | 78 | 76 | | | |
| 4 | 94 | 86 | 80 | 75 | 92 | 85 | 79 | 74 | 82 | 77 | 73 | 80 | 76 | 73 | 78 | 75 | 72 | 70 | | | |
| 5 | 89 | 80 | 73 | 68 | 87 | 79 | 73 | 68 | 77 | 72 | 67 | 75 | 71 | 67 | 74 | 69 | 66 | 65 | | | |
| 6 | 84 | 74 | 68 | 63 | 83 | 73 | 67 | 63 | 72 | 66 | 62 | 70 | 66 | 62 | 69 | 65 | 61 | 60 | | | |
| 7 | 80 | 69 | 63 | 58 | 78 | 69 | 63 | 58 | 67 | 62 | 58 | 66 | 61 | 57 | 65 | 61 | 57 | 56 | | | |
| 8 | 76 | 65 | 59 | 54 | 74 | 65 | 58 | 54 | 63 | 58 | 54 | 62 | 57 | 54 | 61 | 57 | 53 | 52 | | | |
| 9 | 72 | 61 | 55 | 51 | 71 | 61 | 55 | 51 | 60 | 54 | 50 | 59 | 54 | 50 | 58 | 53 | 50 | 49 | | | |
| 10 | 68 | 58 | 52 | 48 | 67 | 57 | 51 | 47 | 57 | 51 | 47 | 56 | 51 | 47 | 55 | 50 | 47 | 46 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 239871 |
| 5° | 233369 |
| 10° | 213267 |
| 15° | 186812 |
| 20° | 160244 |
| 25° | 133798 |
| 30° | 107080 |
| 35° | 80308 |
| 40° | 58281 |
| 45° | 38112 |
| 50° | 23846 |
| 55° | 16133 |
| 60° | 14253 |
| 65° | 13127 |
| 70° | 12374 |
| 75° | 11268 |
| 80° | 10607 |
| 85° | 9057 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 38112 cd/sqm



TEST NUMBER: P1299381

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1LI_6500K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 97.8 | 10.3 |
| 10°-20° | 229.3 | 24.1 |
| 20°-30° | 252.6 | 26.6 |
| 30°-40° | 189.2 | 19.9 |
| 40°-50° | 98.1 | 10.3 |
| 50°-60° | 40.6 | 4.3 |
| 60°-70° | 25.2 | 2.6 |
| 70°-80° | 14.1 | 1.5 |
| 80°-90° | 4.1 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 579.7 | 61.0 |
| 0°-40° | 768.9 | 80.9 |
| 0°-60° | 907.6 | 95.4 |
| 0°-90° | 951.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 951.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1094 | |
| 5° | 1060 | 98 |
| 15° | 823 | 229 |
| 25° | 553 | 253 |
| 35° | 300 | 189 |
| 45° | 123 | 98 |
| 55° | 42 | 41 |
| 65° | 25 | 25 |
| 75° | 13 | 14 |
| 85° | 4 | 4 |
| 90° | 0 | |



TEST NUMBER: P1299381

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1LI_6500K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1093.9 |
| 1° | 1095.1 |
| 2° | 1091.5 |
| 3° | 1084.3 |
| 4° | 1073.4 |
| 5° | 1060.2 |
| 6° | 1043.3 |
| 7° | 1025.3 |
| 8° | 1003.6 |
| 9° | 980.7 |
| 10° | 957.8 |
| 12.5° | 891.5 |
| 15° | 822.9 |
| 17.5° | 754.2 |
| 20° | 686.7 |
| 22.5° | 618.0 |
| 25° | 553.0 |
| 27.5° | 487.9 |
| 30° | 422.9 |
| 32.5° | 359.0 |
| 35° | 300.0 |
| 37.5° | 249.4 |
| 40° | 203.6 |
| 42.5° | 161.4 |
| 45° | 122.9 |
| 47.5° | 92.8 |
| 50° | 69.9 |
| 52.5° | 51.8 |
| 55° | 42.2 |
| 57.5° | 37.3 |
| 60° | 32.5 |
| 62.5° | 28.9 |
| 65° | 25.3 |
| 67.5° | 21.7 |
| 70° | 19.3 |
| 72.5° | 15.7 |
| 75° | 13.3 |
| 77.5° | 10.8 |
| 80° | 8.4 |
| 82.5° | 6.0 |
| 85° | 3.6 |
| 87.5° | 1.2 |
| 90° | 0.0 |

(END OF REPORT)