

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301666

Luminaire Tested: P3AS17R55W2N902750DE010 E3CB1MB\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301666  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R55W2N902750DE010 E3CB1MB\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,  
E3CB1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1589.0 lumens  
Efficiency: N/A  
Efficacy: 81.9 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301666  
CATALOG NUMBER: P3AS17R55W2N902750DE010 E3CB1MB\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1301666

CATALOG NUMBER: P3AS17R55W2N902750DE010 E3CB1MB\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			94
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89			89
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84			84
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	85	83	80	79			79
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74			74
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70			70
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66			66
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63			63
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60			60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	440710
5°	436627
10°	454167
15°	447857
20°	412989
25°	336019
30°	204107
35°	70644
40°	20181
45°	9613
50°	4060
55°	1835
60°	2105
65°	1868
70°	1539
75°	2033
80°	1515
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9613 cd/sqm



TEST NUMBER: P1301666

CATALOG NUMBER: P3AS17R55W2N902750DE010 E3CB1MB\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	191.8	12.1
10°-20°	548.3	34.5
20°-30°	611.3	38.5
30°-40°	200.0	12.6
40°-50°	26.4	1.7
50°-60°	5.6	0.4
60°-70°	3.3	0.2
70°-80°	2.1	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1351.3	85.0
0°-40°	1551.3	97.6
0°-60°	1583.2	99.6
0°-90°	1589.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1589.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2010	
5°	1984	192
15°	1973	548
25°	1389	611
35°	264	200
45°	31	26
55°	5	6
65°	4	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1301666  
CATALOG NUMBER: P3AS17R55W2N902750DE010 E3CB1MB\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2009.8
2.5°	1995.5
5°	1983.6
7.5°	2012.2
10°	2039.7
12.5°	2025.4
15°	1972.8
17.5°	1889.2
20°	1769.8
22.5°	1605.0
25°	1388.8
27.5°	1114.2
30°	806.1
32.5°	494.4
35°	263.9
37.5°	133.7
40°	70.5
42.5°	45.4
45°	31.0
47.5°	21.5
50°	11.9
52.5°	7.2
55°	4.8
57.5°	4.8
60°	4.8
62.5°	3.6
65°	3.6
67.5°	2.4
70°	2.4
72.5°	2.4
75°	2.4
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)