

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299508

Luminaire Tested: P3AS17R20W2N902750DE010 E3D1WMH\_5000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299508  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R20W2N902750DE010 E3D1WMH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 5000K CCT AND, 90CRI ,  
E3D1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1511.0 lumens  
Efficiency: N/A  
Efficacy: 77.9 lumens/watt  
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299508  
CATALOG NUMBER: P3AS17R20W2N902750DE010 E3D1WMH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299508

CATALOG NUMBER: P3AS17R20W2N902750DE010 E3D1WMH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	100
1	115	114	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	98	96	95	95	95	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	93	93	93
4	106	101	98	95	105	100	97	95	99	96	94	97	95	93	95	93	92	91	91	91	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	90	89	89	89	89
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	92	89	88	87	87	87	87
7	99	93	90	87	98	93	89	87	92	89	86	91	88	86	90	87	86	85	85	85	85
8	97	91	87	85	96	91	87	85	90	87	85	89	86	84	88	86	84	83	83	83	83
9	95	89	85	83	94	89	85	83	88	85	83	87	84	83	87	84	82	81	81	81	81
10	93	87	84	81	92	87	83	81	86	83	81	86	83	81	85	83	81	80	80	80	80

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2292075
5°	1929821
10°	1205344
15°	450627
20°	154690
25°	64455
30°	30359
35°	13599
40°	6412
45°	3287
50°	1194
55°	229
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3287 cd/sqm



TEST NUMBER: P1299508

CATALOG NUMBER: P3AS17R20W2N902750DE010 E3D1WMH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	729.1	48.3
10°-20°	600.5	39.7
20°-30°	136.5	9.0
30°-40°	34.7	2.3
40°-50°	8.7	0.6
50°-60°	1.1	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1466.1	97.0
0°-40°	1500.8	99.3
0°-60°	1510.6	100.0
0°-90°	1511.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1511.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10453	
5°	8767	729
15°	1985	601
25°	266	136
35°	51	35
45°	11	9
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1299508  
CATALOG NUMBER: P3AS17R20W2N902750DE010 E3D1WMH\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10452.7
1°	10364.0
2°	10102.9
3°	9728.4
4°	9268.7
5°	8767.2
6°	8208.3
7°	7591.5
8°	6871.9
9°	6158.9
10°	5413.3
11°	4619.9
12°	3827.7
13°	3156.5
14°	2514.9
15°	1985.0
16°	1566.7
17°	1235.9
18°	993.1
19°	807.6
20°	662.9
21°	554.2
22°	462.6
23°	384.6
24°	320.8
25°	266.4
27.5°	174.3
30°	119.9
32.5°	73.8
35°	50.8
37.5°	32.5
40°	22.4
42.5°	15.4
45°	10.6
47.5°	7.1
50°	3.5
52.5°	1.8
55°	0.6
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1299508  
CATALOG NUMBER: P3AS17R20W2N902750DE010 E3D1WMH\_5000K

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)