

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301686

Luminaire Tested: P3AS17R55W2N902750DE010 E3CD1MMS_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301686
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R55W2N902750DE010 E3CD1MMS_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1589.0 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301686
CATALOG NUMBER: P3AS17R55W2N902750DE010 E3CD1MMS_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1301686

CATALOG NUMBER: P3AS17R55W2N902750DE010 E3CD1MMS_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 191.8 | 12.1 |
| 10°-20° | 548.3 | 34.5 |
| 20°-30° | 611.3 | 38.5 |
| 30°-40° | 200.0 | 12.6 |
| 40°-50° | 26.4 | 1.7 |
| 50°-60° | 5.6 | 0.4 |
| 60°-70° | 3.3 | 0.2 |
| 70°-80° | 2.1 | 0.1 |
| 80°-90° | 0.5 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1351.3 | 85.0 |
| 0°-40° | 1551.3 | 97.6 |
| 0°-60° | 1583.2 | 99.6 |
| 0°-90° | 1589.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1589.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2010 | |
| 5° | 1984 | 192 |
| 15° | 1973 | 548 |
| 25° | 1389 | 611 |
| 35° | 264 | 200 |
| 45° | 31 | 26 |
| 55° | 5 | 6 |
| 65° | 4 | 3 |
| 75° | 2 | 2 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1301686
CATALOG NUMBER: P3AS17R55W2N902750DE010 E3CD1MMS_3000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2009.8 |
| 2.5° | 1995.5 |
| 5° | 1983.6 |
| 7.5° | 2012.2 |
| 10° | 2039.7 |
| 12.5° | 2025.4 |
| 15° | 1972.8 |
| 17.5° | 1889.2 |
| 20° | 1769.8 |
| 22.5° | 1605.0 |
| 25° | 1388.8 |
| 27.5° | 1114.2 |
| 30° | 806.1 |
| 32.5° | 494.4 |
| 35° | 263.9 |
| 37.5° | 133.7 |
| 40° | 70.5 |
| 42.5° | 45.4 |
| 45° | 31.0 |
| 47.5° | 21.5 |
| 50° | 11.9 |
| 52.5° | 7.2 |
| 55° | 4.8 |
| 57.5° | 4.8 |
| 60° | 4.8 |
| 62.5° | 3.6 |
| 65° | 3.6 |
| 67.5° | 2.4 |
| 70° | 2.4 |
| 72.5° | 2.4 |
| 75° | 2.4 |
| 77.5° | 1.2 |
| 80° | 1.2 |
| 82.5° | 1.2 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)