

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299577

Luminaire Tested: P3AS17R20W2N902750DE010 E3PHLD1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299577
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R20W2N902750DE010 E3PHLD1MW_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 4000K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 834.0 lumens
Efficiency: N/A
Efficacy: 43.0 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299577
CATALOG NUMBER: P3AS17R20W2N902750DE010 E3PHLD1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299577

CATALOG NUMBER: P3AS17R20W2N902750DE010 E3PHLD1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	85	82	80
3	98	90	83	78	95	88	82	78	85	81	77	83	79	75	80	77	74	72
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	81	70	63	58	79	70	63	58	68	62	58	66	61	57	65	60	57	55
7	76	66	59	54	75	65	58	53	63	58	53	62	57	53	61	56	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	236516
5°	219722
10°	186058
15°	145654
20°	114623
25°	91360
30°	73480
35°	59910
40°	49550
45°	41741
50°	35786
55°	30737
60°	26840
65°	23608
70°	20196
75°	17792
80°	13259
85°	8806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 41741 cd/sqm



TEST NUMBER: P1299577

CATALOG NUMBER: P3AS17R20W2N902750DE010 E3PHLD1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.1	10.8
10°-20°	179.6	21.5
20°-30°	174.4	20.9
30°-40°	140.9	16.9
40°-50°	104.7	12.6
50°-60°	72.7	8.7
60°-70°	45.6	5.5
70°-80°	22.1	2.7
80°-90°	3.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	444.1	53.3
0°-40°	585.1	70.1
0°-60°	762.5	91.4
0°-90°	834.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	834.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1079	
5°	998	90
15°	642	180
25°	378	174
35°	224	141
45°	135	105
55°	80	73
65°	46	46
75°	21	22
85°	4	4
90°	0	



TEST NUMBER: P1299577

CATALOG NUMBER: P3AS17R20W2N902750DE010 E3PHLD1MW_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1078.6
2.5°	1054.1
5°	998.2
7.5°	923.0
10°	835.6
12.5°	739.5
15°	641.6
17.5°	561.2
20°	491.2
22.5°	430.1
25°	377.6
27.5°	332.2
30°	290.2
32.5°	255.2
35°	223.8
37.5°	195.8
40°	173.1
42.5°	152.1
45°	134.6
47.5°	118.9
50°	104.9
52.5°	92.7
55°	80.4
57.5°	69.9
60°	61.2
62.5°	54.2
65°	45.5
67.5°	38.5
70°	31.5
72.5°	26.2
75°	21.0
77.5°	15.7
80°	10.5
82.5°	5.2
85°	3.5
87.5°	0.0
90°	0.0

(END OF REPORT)