

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301767

Luminaire Tested: P3AS17R55W2N902750DE010 E3DLD1MW_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301767
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R55W2N902750DE010 E3DLD1MW_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3500K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1026.0 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301767
CATALOG NUMBER: P3AS17R55W2N902750DE010 E3DLD1MW_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1301767
 CATALOG NUMBER: P3AS17R55W2N902750DE010 E3DLD1MW_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	192923
5°	190446
10°	182940
15°	171102
20°	156090
25°	139266
30°	121816
35°	101214
40°	79778
45°	54114
50°	33056
55°	17127
60°	15964
65°	15099
70°	13977
75°	12285
80°	12249
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 54114 cd/sqm



TEST NUMBER: P1301767

CATALOG NUMBER: P3AS17R55W2N902750DE010 E3DLD1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.1	7.9
10°-20°	210.7	20.5
20°-30°	263.8	25.7
30°-40°	235.5	23.0
40°-50°	137.9	13.4
50°-60°	47.6	4.6
60°-70°	28.8	2.8
70°-80°	16.0	1.6
80°-90°	4.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	555.6	54.2
0°-40°	791.1	77.1
0°-60°	976.6	95.2
0°-90°	1026.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1026.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	880	
5°	865	81
15°	754	211
25°	576	264
35°	378	235
45°	174	138
55°	45	48
65°	29	29
75°	14	16
85°	4	5
90°	0	



TEST NUMBER: P1301767
CATALOG NUMBER: P3AS17R55W2N902750DE010 E3DLD1MW_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	879.8
2.5°	874.9
5°	865.2
7.5°	845.8
10°	821.6
12.5°	791.3
15°	753.7
17.5°	713.7
20°	668.9
22.5°	622.9
25°	575.6
27.5°	528.3
30°	481.1
32.5°	430.2
35°	378.1
37.5°	327.2
40°	278.7
42.5°	226.6
45°	174.5
47.5°	133.3
50°	96.9
52.5°	63.0
55°	44.8
57.5°	40.0
60°	36.4
62.5°	32.7
65°	29.1
67.5°	25.4
70°	21.8
72.5°	18.2
75°	14.5
77.5°	12.1
80°	9.7
82.5°	6.1
85°	3.6
87.5°	2.4
90°	0.0

(END OF REPORT)