

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301771

Luminaire Tested: P3AS17R55W2N902750DE010 E3DLD1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301771
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R55W2N902750DE010 E3DLD1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1011.0 lumens
Efficiency: N/A
Efficacy: 52.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301771
CATALOG NUMBER: P3AS17R55W2N902750DE010 E3DLD1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1301771
 CATALOG NUMBER: P3AS17R55W2N902750DE010 E3DLD1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			74
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			68
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			52
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48			48
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	190094
5°	187673
10°	180268
15°	168605
20°	153803
25°	137234
30°	120018
35°	99742
40°	78604
45°	53308
50°	32579
55°	16898
60°	15700
65°	14891
70°	13784
75°	12115
80°	12123
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 53308 cd/sqm



TEST NUMBER: P1301771

CATALOG NUMBER: P3AS17R55W2N902750DE010 E3DLD1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.0	7.9
10°-20°	207.6	20.5
20°-30°	259.9	25.7
30°-40°	232.0	23.0
40°-50°	135.8	13.4
50°-60°	46.9	4.6
60°-70°	28.4	2.8
70°-80°	15.7	1.6
80°-90°	4.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	547.5	54.2
0°-40°	779.5	77.1
0°-60°	962.3	95.2
0°-90°	1011.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1011.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	867	
5°	853	80
15°	743	208
25°	567	260
35°	373	232
45°	172	136
55°	44	47
65°	29	28
75°	14	16
85°	4	5
90°	0	



TEST NUMBER: P1301771
CATALOG NUMBER: P3AS17R55W2N902750DE010 E3DLD1WH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	866.9
2.5°	862.1
5°	852.6
7.5°	833.5
10°	809.6
12.5°	779.7
15°	742.7
17.5°	703.3
20°	659.1
22.5°	613.8
25°	567.2
27.5°	520.6
30°	474.0
32.5°	423.9
35°	372.6
37.5°	322.4
40°	274.6
42.5°	223.3
45°	171.9
47.5°	131.3
50°	95.5
52.5°	62.1
55°	44.2
57.5°	39.4
60°	35.8
62.5°	32.2
65°	28.7
67.5°	25.1
70°	21.5
72.5°	17.9
75°	14.3
77.5°	11.9
80°	9.6
82.5°	6.0
85°	3.6
87.5°	2.4
90°	0.0

(END OF REPORT)