

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301867

Luminaire Tested: P3AS17R55W2N902765DE010 E3D1WH\_4000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301867  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R55W2N902765DE010 E3D1WH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 4000K CCT AND, 90CRI ,  
E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1564.0 lumens  
Efficiency: N/A  
Efficacy: 80.6 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301867  
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3D1WH\_4000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1301867

CATALOG NUMBER: P3AS17R55W2N902765DE010 E3D1WH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	192.3	12.3
10°-20°	547.9	35.0
20°-30°	609.0	38.9
30°-40°	189.6	12.1
40°-50°	22.8	1.5
50°-60°	1.8	0.1
60°-70°	0.6	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1349.2	86.3
0°-40°	1538.8	98.4
0°-60°	1563.3	100.0
0°-90°	1564.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1564.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2068	
5°	1988	192
15°	1968	548
25°	1382	609
35°	254	190
45°	27	23
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1301867

CATALOG NUMBER: P3AS17R55W2N902765DE010 E3D1WH\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2068.3
1°	2060.6
2°	2040.4
3°	2015.4
4°	1992.9
5°	1987.5
6°	1993.5
7°	2005.9
8°	2020.2
9°	2031.5
10°	2035.0
11°	2032.7
12°	2023.2
13°	2008.3
14°	1991.1
15°	1967.9
16°	1941.2
17°	1907.3
18°	1869.3
19°	1823.5
20°	1771.8
21°	1713.0
22°	1643.5
23°	1566.8
24°	1478.9
25°	1382.0
26°	1275.7
27°	1162.8
28°	1042.2
29°	918.0
30°	791.4
31°	664.3
32°	540.1
32.5°	484.8
33°	427.8
34°	331.0
35°	253.7
36°	193.1
37°	143.2
37.5°	122.4
38°	106.4
39°	80.8
40°	65.4
42.5°	41.6
45°	26.7



TEST NUMBER: P1301867  
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3D1WH\_4000K

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	16.0
50°	7.1
52.5°	2.4
55°	1.2
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)