

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299726

Luminaire Tested: P3AS17R20W2N902765DE010 E3PH1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299726
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R20W2N902765DE010 E3PH1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 5000K CCT AND, 90CRI ,
E3PH1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1089.0 lumens
Efficiency: N/A
Efficacy: 56.1 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.32
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299726
CATALOG NUMBER: P3AS17R20W2N902765DE010 E3PH1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299726

CATALOG NUMBER: P3AS17R20W2N902765DE010 E3PH1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 106 | 104 | 104 | 103 | 101 | 100 | 100 | 98 | 98 | 98 | 98 |
| 2 | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 104 | 105 | 104 | 102 | 102 | 101 | 100 | 100 | 99 | 98 | 97 | 97 | 97 | 97 |
| 3 | 110 | 107 | 104 | 101 | 109 | 105 | 103 | 101 | 103 | 101 | 99 | 101 | 99 | 98 | 99 | 97 | 96 | 95 | 95 | 95 | 95 |
| 4 | 108 | 104 | 101 | 98 | 107 | 103 | 100 | 98 | 101 | 98 | 97 | 99 | 97 | 95 | 97 | 96 | 94 | 93 | 93 | 93 | 93 |
| 5 | 106 | 101 | 98 | 96 | 105 | 100 | 97 | 95 | 99 | 96 | 94 | 97 | 95 | 94 | 96 | 94 | 93 | 92 | 92 | 92 | 92 |
| 6 | 104 | 99 | 96 | 93 | 103 | 98 | 95 | 93 | 97 | 94 | 93 | 96 | 94 | 92 | 95 | 93 | 91 | 91 | 91 | 91 | 91 |
| 7 | 102 | 97 | 94 | 92 | 101 | 96 | 93 | 91 | 95 | 93 | 91 | 95 | 92 | 90 | 94 | 92 | 90 | 89 | 89 | 89 | 89 |
| 8 | 100 | 95 | 92 | 90 | 99 | 95 | 92 | 90 | 94 | 91 | 89 | 93 | 91 | 89 | 92 | 90 | 89 | 88 | 88 | 88 | 88 |
| 9 | 99 | 94 | 90 | 88 | 98 | 93 | 90 | 88 | 92 | 90 | 88 | 92 | 89 | 88 | 91 | 89 | 88 | 87 | 87 | 87 | 87 |
| 10 | 97 | 92 | 89 | 87 | 96 | 92 | 89 | 87 | 91 | 88 | 87 | 91 | 88 | 87 | 90 | 88 | 86 | 86 | 86 | 86 | 86 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 2165484 |
| 5° | 1663258 |
| 10° | 1024675 |
| 15° | 298208 |
| 20° | 39787 |
| 25° | 11783 |
| 30° | 3520 |
| 35° | 455 |
| 40° | 487 |
| 45° | 0 |
| 50° | 0 |
| 55° | 0 |
| 60° | 0 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 0 cd/sqm



TEST NUMBER: P1299726

CATALOG NUMBER: P3AS17R20W2N902765DE010 E3PH1MW_5000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 629.3 | 57.8 |
| 10°-20° | 429.2 | 39.4 |
| 20°-30° | 27.6 | 2.5 |
| 30°-40° | 2.7 | 0.2 |
| 40°-50° | 0.2 | 0.0 |
| 50°-60° | 0.0 | 0.0 |
| 60°-70° | 0.0 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1086.1 | 99.7 |
| 0°-40° | 1088.8 | 100.0 |
| 0°-60° | 1089.0 | 100.0 |
| 0°-90° | 1089.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1089.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 9875 | |
| 5° | 7556 | 629 |
| 15° | 1314 | 429 |
| 25° | 49 | 28 |
| 35° | 2 | 3 |
| 45° | 0 | 0 |
| 55° | 0 | 0 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1299726
CATALOG NUMBER: P3AS17R20W2N902765DE010 E3PH1MW_5000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 9875.4 |
| 2.5° | 8904.6 |
| 5° | 7556.2 |
| 7.5° | 6061.7 |
| 10° | 4601.9 |
| 12.5° | 2886.4 |
| 15° | 1313.6 |
| 17.5° | 415.8 |
| 20° | 170.5 |
| 22.5° | 90.5 |
| 25° | 48.7 |
| 27.5° | 24.4 |
| 30° | 13.9 |
| 32.5° | 7.0 |
| 35° | 1.7 |
| 37.5° | 1.7 |
| 40° | 1.7 |
| 42.5° | 0.0 |
| 45° | 0.0 |
| 47.5° | 0.0 |
| 50° | 0.0 |
| 52.5° | 0.0 |
| 55° | 0.0 |
| 57.5° | 0.0 |
| 60° | 0.0 |
| 62.5° | 0.0 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)