

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299796

Luminaire Tested: P3AS17R25W2N902750DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299796
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R25W2N902750DE010 E3DL1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 613.0 lumens
Efficiency: N/A
Efficacy: 31.6 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299796
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299796

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.9	24.1
10°-20°	241.6	39.4
20°-30°	138.1	22.5
30°-40°	54.5	8.9
40°-50°	16.7	2.7
50°-60°	6.6	1.1
60°-70°	4.4	0.7
70°-80°	2.5	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.5	86.1
0°-40°	582.0	94.9
0°-60°	605.3	98.7
0°-90°	613.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	613.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1793	
5°	1667	148
15°	879	242
25°	292	138
35°	83	54
45°	20	17
55°	7	7
65°	5	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1299796
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1793.2
1°	1789.7
2°	1775.1
3°	1749.3
4°	1713.5
5°	1666.7
6°	1611.6
7°	1549.5
8°	1477.5
9°	1403.6
10°	1319.9
11°	1237.3
12°	1146.5
13°	1056.8
14°	964.9
15°	878.7
17.5°	681.3
20°	517.3
22.5°	388.4
25°	291.7
27.5°	216.2
30°	158.8
32.5°	114.8
35°	82.6
37.5°	58.6
40°	41.0
42.5°	28.1
45°	19.9
47.5°	14.1
50°	10.5
52.5°	8.2
55°	7.0
57.5°	6.4
60°	5.3
62.5°	4.7
65°	4.7
67.5°	4.1
70°	3.5
72.5°	2.9
75°	2.3
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.6



TEST NUMBER: P1299796
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)