

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299799

Luminaire Tested: P3AS17R25W2N902750DE010 E3DL1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299799
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R25W2N902750DE010 E3DL1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 618.0 lumens
Efficiency: N/A
Efficacy: 31.9 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299799
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DL1GPH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299799

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DL1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	396416
5°	369865
10°	296276
15°	201114
20°	121694
25°	71157
30°	40538
35°	22299
40°	11822
45°	6233
50°	3616
55°	2714
60°	2324
65°	2439
70°	2244
75°	2033
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6233 cd/sqm



TEST NUMBER: P1299799

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DL1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.1	24.1
10°-20°	243.6	39.4
20°-30°	139.2	22.5
30°-40°	54.9	8.9
40°-50°	16.8	2.7
50°-60°	6.7	1.1
60°-70°	4.4	0.7
70°-80°	2.5	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	531.8	86.1
0°-40°	586.8	94.9
0°-60°	610.3	98.7
0°-90°	618.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	618.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1808	
5°	1680	149
15°	886	244
25°	294	139
35°	83	55
45°	20	17
55°	7	7
65°	5	4
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1299799
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DL1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1807.8
1°	1804.3
2°	1789.5
3°	1763.5
4°	1727.5
5°	1680.3
6°	1624.8
7°	1562.1
8°	1489.5
9°	1415.1
10°	1330.6
11°	1247.4
12°	1155.8
13°	1065.4
14°	972.7
15°	885.9
17.5°	686.9
20°	521.5
22.5°	391.6
25°	294.1
27.5°	217.9
30°	160.1
32.5°	115.8
35°	83.3
37.5°	59.1
40°	41.3
42.5°	28.3
45°	20.1
47.5°	14.2
50°	10.6
52.5°	8.3
55°	7.1
57.5°	6.5
60°	5.3
62.5°	4.7
65°	4.7
67.5°	4.1
70°	3.5
72.5°	3.0
75°	2.4
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.6



TEST NUMBER: P1299799
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DL1GPH_5000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)