

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301945

Luminaire Tested: P3AS17R55W2N902765DE010 E3DLD1WMH\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301945  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R55W2N902765DE010 E3DLD1WMH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 4000K CCT AND, 90CRI ,  
E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1026.0 lumens  
Efficiency: N/A  
Efficacy: 52.9 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301945  
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLD1WMH\_4000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1301945

CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLD1WMH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.1	7.9
10°-20°	210.7	20.5
20°-30°	263.8	25.7
30°-40°	235.5	23.0
40°-50°	137.9	13.4
50°-60°	47.6	4.6
60°-70°	28.8	2.8
70°-80°	16.0	1.6
80°-90°	4.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	555.6	54.2
0°-40°	791.1	77.1
0°-60°	976.6	95.2
0°-90°	1026.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1026.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	880	
5°	865	81
15°	754	211
25°	576	264
35°	378	235
45°	174	138
55°	45	48
65°	29	29
75°	14	16
85°	4	5
90°	0	



TEST NUMBER: P1301945  
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLD1WMH\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	879.8
2.5°	874.9
5°	865.2
7.5°	845.8
10°	821.6
12.5°	791.3
15°	753.7
17.5°	713.7
20°	668.9
22.5°	622.9
25°	575.6
27.5°	528.3
30°	481.1
32.5°	430.2
35°	378.1
37.5°	327.2
40°	278.7
42.5°	226.6
45°	174.5
47.5°	133.3
50°	96.9
52.5°	63.0
55°	44.8
57.5°	40.0
60°	36.4
62.5°	32.7
65°	29.1
67.5°	25.4
70°	21.8
72.5°	18.2
75°	14.5
77.5°	12.1
80°	9.7
82.5°	6.1
85°	3.6
87.5°	2.4
90°	0.0

(END OF REPORT)