

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299806

Luminaire Tested: P3AS17R25W2N902750DE010 E3DL1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R25W2N902750DE010 E3DL1LI_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1250.0 lumens
Efficiency: N/A
Efficacy: 64.4 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299806
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DL1LI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299806
 CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DL1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	801822
5°	748094
10°	599276
15°	406790
20°	246141
25°	143936
30°	81962
35°	45079
40°	23931
45°	12590
50°	7335
55°	5467
60°	4736
65°	4981
70°	4616
75°	4067
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12590 cd/sqm



TEST NUMBER: P1299806

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DL1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.6	24.1
10°-20°	492.6	39.4
20°-30°	281.5	22.5
30°-40°	111.1	8.9
40°-50°	34.0	2.7
50°-60°	13.4	1.1
60°-70°	9.1	0.7
70°-80°	5.1	0.4
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1075.7	86.1
0°-40°	1186.8	94.9
0°-60°	1234.3	98.7
0°-90°	1250.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1250.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3657	
5°	3399	302
15°	1792	493
25°	595	281
35°	168	111
45°	41	34
55°	14	13
65°	10	9
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P1299806
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DL1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3656.6
1°	3649.5
2°	3619.6
3°	3567.0
4°	3494.2
5°	3398.6
6°	3286.3
7°	3159.7
8°	3012.7
9°	2862.2
10°	2691.4
11°	2523.0
12°	2337.8
13°	2155.0
14°	1967.5
15°	1791.9
17.5°	1389.3
20°	1054.8
22.5°	792.0
25°	594.9
27.5°	440.8
30°	323.7
32.5°	234.1
35°	168.4
37.5°	119.5
40°	83.6
42.5°	57.3
45°	40.6
47.5°	28.7
50°	21.5
52.5°	16.7
55°	14.3
57.5°	13.1
60°	10.8
62.5°	9.6
65°	9.6
67.5°	8.4
70°	7.2
72.5°	6.0
75°	4.8
77.5°	3.6
80°	2.4
82.5°	2.4
85°	1.2
87.5°	1.2



TEST NUMBER: P1299806
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DL1LI_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)