

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301974

Luminaire Tested: P3AS17R55W2N902765DE010 E3DLP1WH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301974  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R55W2N902765DE010 E3DLP1WH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3500K CCT AND, 90CRI ,  
E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1321.0 lumens  
Efficiency: N/A  
Efficacy: 68.1 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301974  
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLP1WH\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1301974

CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLP1WH\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93				93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87				87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	84	87	85	82	81				81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75				75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66				66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62				62
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58				58
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55				55
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52				52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	362734
5°	359057
10°	346754
15°	320501
20°	276571
25°	218432
30°	154961
35°	99930
40°	60027
45°	33833
50°	18183
55°	6499
60°	5833
65°	5656
70°	5450
75°	5168
80°	4546
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 33833 cd/sqm



TEST NUMBER: P1301974

CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLP1WH\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.4	11.6
10°-20°	390.4	29.6
20°-30°	409.1	31.0
30°-40°	238.7	18.1
40°-50°	89.3	6.8
50°-60°	21.0	1.6
60°-70°	10.8	0.8
70°-80°	6.4	0.5
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	953.0	72.1
0°-40°	1191.7	90.2
0°-60°	1302.0	98.6
0°-90°	1321.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1321.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1654	
5°	1631	153
15°	1412	390
25°	903	409
35°	373	239
45°	109	89
55°	17	21
65°	11	11
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P1301974  
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLP1WH\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1654.2
2.5°	1649.4
5°	1631.2
7.5°	1602.1
10°	1557.3
12.5°	1494.2
15°	1411.8
17.5°	1307.6
20°	1185.2
22.5°	1048.3
25°	902.8
27.5°	753.8
30°	612.0
32.5°	483.5
35°	373.3
37.5°	283.6
40°	209.7
42.5°	150.3
45°	109.1
47.5°	78.8
50°	53.3
52.5°	30.3
55°	17.0
57.5°	14.5
60°	13.3
62.5°	12.1
65°	10.9
67.5°	9.7
70°	8.5
72.5°	7.3
75°	6.1
77.5°	4.8
80°	3.6
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)