

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301977

Luminaire Tested: P3AS17R55W2N902765DE010 E3DLP1WH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R55W2N902765DE010 E3DLP1WH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 6500K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1312.9 lumens
Efficiency: N/A
Efficacy: 67.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301977
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLP1WH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1301977

CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLP1WH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	95	90	86	92	88	85	89	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	360541
5°	356878
10°	344638
15°	318572
20°	274891
25°	217125
30°	154024
35°	99314
40°	59655
45°	33616
50°	18080
55°	6461
60°	5789
65°	5604
70°	5386
75°	5083
80°	4546
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 33616 cd/sqm



TEST NUMBER: P1301977

CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLP1WH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.5	11.6
10°-20°	388.0	29.6
20°-30°	406.7	31.0
30°-40°	237.3	18.1
40°-50°	88.8	6.8
50°-60°	20.9	1.6
60°-70°	10.7	0.8
70°-80°	6.3	0.5
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	947.2	72.1
0°-40°	1184.4	90.2
0°-60°	1294.1	98.6
0°-90°	1312.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1312.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1644	
5°	1621	152
15°	1403	388
25°	897	407
35°	371	237
45°	108	89
55°	17	21
65°	11	11
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P1301977
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLP1WH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1644.2
2.5°	1639.4
5°	1621.3
7.5°	1592.4
10°	1547.8
12.5°	1485.2
15°	1403.3
17.5°	1299.7
20°	1178.0
22.5°	1041.9
25°	897.4
27.5°	749.2
30°	608.3
32.5°	480.6
35°	371.0
37.5°	281.9
40°	208.4
42.5°	149.4
45°	108.4
47.5°	78.3
50°	53.0
52.5°	30.1
55°	16.9
57.5°	14.5
60°	13.2
62.5°	12.0
65°	10.8
67.5°	9.6
70°	8.4
72.5°	7.2
75°	6.0
77.5°	4.8
80°	3.6
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)