

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299863

Luminaire Tested: P3AS17R25W2N902750DE010 E3DLP1H\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299863  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R25W2N902750DE010 E3DLP1H\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,  
E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 777.0 lumens  
Efficiency: N/A  
Efficacy: 40.1 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299863  
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DLP1H\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299863

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DLP1H\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 95  | 93  | 93  | 93  | 93  |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 97  | 94  | 92  | 94  | 92  | 90  | 92  | 90  | 88  | 86  | 86  | 86  | 86  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 86  | 91  | 87  | 84  | 89  | 86  | 83  | 87  | 84  | 82  | 80  | 80  | 80  | 80  |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  | 84  | 80  | 77  | 82  | 79  | 76  | 75  | 75  | 75  | 75  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 77  | 73  | 81  | 76  | 73  | 79  | 75  | 72  | 78  | 74  | 71  | 70  | 70  | 70  | 70  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 72  | 68  | 77  | 72  | 68  | 75  | 71  | 67  | 74  | 70  | 67  | 66  | 66  | 66  | 66  |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  | 71  | 67  | 63  | 70  | 66  | 63  | 62  | 62  | 62  | 62  |
| 8   | 80  | 70  | 65  | 60  | 79  | 70  | 64  | 60  | 69  | 64  | 60  | 68  | 63  | 60  | 67  | 63  | 60  | 58  | 58  | 58  | 58  |
| 9   | 76  | 67  | 61  | 57  | 75  | 66  | 61  | 57  | 65  | 60  | 57  | 65  | 60  | 57  | 64  | 59  | 56  | 55  | 55  | 55  | 55  |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  | 62  | 57  | 54  | 62  | 57  | 54  | 61  | 57  | 54  | 52  | 52  | 52  | 52  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 282105 |
| 5°  | 270635 |
| 10° | 237092 |
| 15° | 190580 |
| 20° | 146429 |
| 25° | 110789 |
| 30° | 80063  |
| 35° | 53190  |
| 40° | 32260  |
| 45° | 18793  |
| 50° | 11974  |
| 55° | 9711   |
| 60° | 8508   |
| 65° | 7524   |
| 70° | 6219   |
| 75° | 6185   |
| 80° | 4546   |
| 85° | 6038   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18793 cd/sqm



TEST NUMBER: P1299863

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DLP1H\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 111.9  | 14.4      |
| 10°-20°   | 232.1  | 29.9      |
| 20°-30°   | 209.9  | 27.0      |
| 30°-40°   | 126.1  | 16.2      |
| 40°-50°   | 50.1   | 6.4       |
| 50°-60°   | 23.1   | 3.0       |
| 60°-70°   | 14.1   | 1.8       |
| 70°-80°   | 7.5    | 1.0       |
| 80°-90°   | 2.1    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 554.0  | 71.3      |
| 0°-40°    | 680.1  | 87.5      |
| 0°-60°    | 753.3  | 96.9      |
| 0°-90°    | 777.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 777.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1286 |      |
| 5°  | 1230 | 112  |
| 15° | 840  | 232  |
| 25° | 458  | 210  |
| 35° | 199  | 126  |
| 45° | 61   | 50   |
| 55° | 25   | 23   |
| 65° | 14   | 14   |
| 75° | 7    | 8    |
| 85° | 2    | 2    |
| 90° | 0    |      |



TEST NUMBER: P1299863  
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DLP1H\_4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1286.5 |
| 1°    | 1286.5 |
| 2°    | 1280.4 |
| 3°    | 1267.1 |
| 4°    | 1250.1 |
| 5°    | 1229.5 |
| 6°    | 1202.9 |
| 7°    | 1172.6 |
| 8°    | 1137.5 |
| 9°    | 1102.3 |
| 10°   | 1064.8 |
| 11°   | 1021.2 |
| 12°   | 976.3  |
| 13°   | 931.5  |
| 14°   | 886.7  |
| 15°   | 839.5  |
| 17.5° | 728.0  |
| 20°   | 627.5  |
| 22.5° | 536.6  |
| 25°   | 457.9  |
| 27.5° | 384.0  |
| 30°   | 316.2  |
| 32.5° | 254.4  |
| 35°   | 198.7  |
| 37.5° | 151.4  |
| 40°   | 112.7  |
| 42.5° | 82.4   |
| 45°   | 60.6   |
| 47.5° | 46.0   |
| 50°   | 35.1   |
| 52.5° | 29.1   |
| 55°   | 25.4   |
| 57.5° | 21.8   |
| 60°   | 19.4   |
| 62.5° | 15.7   |
| 65°   | 14.5   |
| 67.5° | 12.1   |
| 70°   | 9.7    |
| 72.5° | 8.5    |
| 75°   | 7.3    |
| 77.5° | 6.1    |
| 80°   | 3.6    |
| 82.5° | 2.4    |
| 85°   | 2.4    |
| 87.5° | 1.2    |



TEST NUMBER: P1299863  
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DLP1H\_4000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)