

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299988

Luminaire Tested: P3AS17R25W2N902765DE010 E3DL1MW\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299988  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R25W2N902765DE010 E3DL1MW\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,  
E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1261.9 lumens  
Efficiency: N/A  
Efficacy: 65.0 lumens/watt  
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299988  
CATALOG NUMBER: P3AS17R25W2N902765DE010 E3DL1MW\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299988

CATALOG NUMBER: P3AS17R25W2N902765DE010 E3DL1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 95  | 95  | 95  | 95  |
| 2   | 110 | 105 | 102 | 99  | 107 | 104 | 101 | 98  | 101 | 98  | 96  | 98  | 96  | 94  | 95  | 93  | 92  | 90  | 90  | 90  | 90  |
| 3   | 105 | 100 | 96  | 92  | 103 | 98  | 95  | 91  | 96  | 93  | 90  | 94  | 91  | 89  | 91  | 89  | 87  | 86  | 86  | 86  | 86  |
| 4   | 101 | 95  | 90  | 87  | 99  | 94  | 89  | 86  | 92  | 88  | 85  | 90  | 87  | 84  | 88  | 85  | 83  | 82  | 82  | 82  | 82  |
| 5   | 97  | 90  | 85  | 82  | 96  | 89  | 85  | 81  | 88  | 84  | 81  | 86  | 83  | 80  | 85  | 82  | 79  | 78  | 78  | 78  | 78  |
| 6   | 94  | 86  | 81  | 78  | 92  | 86  | 81  | 78  | 84  | 80  | 77  | 83  | 79  | 77  | 82  | 78  | 76  | 75  | 75  | 75  | 75  |
| 7   | 90  | 83  | 78  | 74  | 89  | 82  | 77  | 74  | 81  | 77  | 74  | 80  | 76  | 73  | 79  | 75  | 73  | 72  | 72  | 72  | 72  |
| 8   | 87  | 79  | 74  | 71  | 86  | 79  | 74  | 71  | 78  | 74  | 71  | 77  | 73  | 70  | 76  | 73  | 70  | 69  | 69  | 69  | 69  |
| 9   | 84  | 76  | 71  | 68  | 83  | 76  | 71  | 68  | 75  | 71  | 68  | 74  | 70  | 68  | 73  | 70  | 67  | 66  | 66  | 66  | 66  |
| 10  | 81  | 73  | 69  | 65  | 80  | 73  | 68  | 65  | 72  | 68  | 65  | 72  | 68  | 65  | 71  | 67  | 65  | 64  | 64  | 64  | 64  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 809518 |
| 5°  | 755270 |
| 10° | 605021 |
| 15° | 410695 |
| 20° | 248498 |
| 25° | 145315 |
| 30° | 82747  |
| 35° | 45534  |
| 40° | 24160  |
| 45° | 12714  |
| 50° | 7403   |
| 55° | 5543   |
| 60° | 4780   |
| 65° | 4981   |
| 70° | 4616   |
| 75° | 4067   |
| 80° | 3031   |
| 85° | 3019   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12714 cd/sqm



TEST NUMBER: P1299988

CATALOG NUMBER: P3AS17R25W2N902765DE010 E3DL1MW\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 304.5  | 24.1      |
| 10°-20°   | 497.4  | 39.4      |
| 20°-30°   | 284.2  | 22.5      |
| 30°-40°   | 112.2  | 8.9       |
| 40°-50°   | 34.4   | 2.7       |
| 50°-60°   | 13.6   | 1.1       |
| 60°-70°   | 9.1    | 0.7       |
| 70°-80°   | 5.1    | 0.4       |
| 80°-90°   | 1.6    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1086.0 | 86.1      |
| 0°-40°    | 1198.2 | 94.9      |
| 0°-60°    | 1246.2 | 98.8      |
| 0°-90°    | 1261.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1261.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3692 |      |
| 5°  | 3431 | 304  |
| 15° | 1809 | 497  |
| 25° | 601  | 284  |
| 35° | 170  | 112  |
| 45° | 41   | 34   |
| 55° | 14   | 14   |
| 65° | 10   | 9    |
| 75° | 5    | 5    |
| 85° | 1    | 2    |
| 90° | 0    |      |



TEST NUMBER: P1299988

CATALOG NUMBER: P3AS17R25W2N902765DE010 E3DL1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3691.7 |
| 1°    | 3684.5 |
| 2°    | 3654.3 |
| 3°    | 3601.3 |
| 4°    | 3527.7 |
| 5°    | 3431.2 |
| 6°    | 3317.9 |
| 7°    | 3190.0 |
| 8°    | 3041.7 |
| 9°    | 2889.7 |
| 10°   | 2717.2 |
| 11°   | 2547.2 |
| 12°   | 2360.2 |
| 13°   | 2175.7 |
| 14°   | 1986.4 |
| 15°   | 1809.1 |
| 17.5° | 1402.6 |
| 20°   | 1064.9 |
| 22.5° | 799.6  |
| 25°   | 600.6  |
| 27.5° | 445.0  |
| 30°   | 326.8  |
| 32.5° | 236.4  |
| 35°   | 170.1  |
| 37.5° | 120.6  |
| 40°   | 84.4   |
| 42.5° | 57.9   |
| 45°   | 41.0   |
| 47.5° | 28.9   |
| 50°   | 21.7   |
| 52.5° | 16.9   |
| 55°   | 14.5   |
| 57.5° | 13.3   |
| 60°   | 10.9   |
| 62.5° | 9.6    |
| 65°   | 9.6    |
| 67.5° | 8.4    |
| 70°   | 7.2    |
| 72.5° | 6.0    |
| 75°   | 4.8    |
| 77.5° | 3.6    |
| 80°   | 2.4    |
| 82.5° | 2.4    |
| 85°   | 1.2    |
| 87.5° | 1.2    |



TEST NUMBER: P1299988  
CATALOG NUMBER: P3AS17R25W2N902765DE010 E3DL1MW\_5000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)