

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302100

Luminaire Tested: P3AS17R60W2N902750DE010 E3DLP1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302100
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R60W2N902750DE010 E3DLP1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 426.0 lumens
Efficiency: N/A
Efficacy: 22.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302100
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302100
 CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 | | | |
| 2 | 107 | 101 | 97 | 93 | 104 | 100 | 96 | 92 | 96 | 93 | 90 | 93 | 91 | 88 | 91 | 88 | 86 | 85 | | | |
| 3 | 101 | 94 | 88 | 84 | 99 | 92 | 87 | 83 | 90 | 86 | 82 | 87 | 84 | 81 | 85 | 82 | 80 | 78 | | | |
| 4 | 95 | 87 | 81 | 77 | 93 | 86 | 80 | 76 | 84 | 79 | 75 | 82 | 78 | 74 | 80 | 76 | 73 | 72 | | | |
| 5 | 90 | 81 | 75 | 70 | 88 | 80 | 74 | 70 | 78 | 73 | 69 | 77 | 72 | 69 | 75 | 71 | 68 | 66 | | | |
| 6 | 85 | 76 | 69 | 65 | 84 | 75 | 69 | 65 | 73 | 68 | 64 | 72 | 67 | 64 | 71 | 66 | 63 | 62 | | | |
| 7 | 81 | 71 | 65 | 60 | 79 | 70 | 64 | 60 | 69 | 64 | 60 | 68 | 63 | 59 | 67 | 62 | 59 | 57 | | | |
| 8 | 77 | 67 | 60 | 56 | 75 | 66 | 60 | 56 | 65 | 60 | 56 | 64 | 59 | 55 | 63 | 58 | 55 | 54 | | | |
| 9 | 73 | 63 | 57 | 52 | 72 | 62 | 56 | 52 | 61 | 56 | 52 | 60 | 55 | 52 | 60 | 55 | 52 | 50 | | | |
| 10 | 69 | 59 | 53 | 49 | 68 | 59 | 53 | 49 | 58 | 53 | 49 | 57 | 52 | 49 | 56 | 52 | 49 | 47 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 107952 |
| 5° | 105547 |
| 10° | 98818 |
| 15° | 88650 |
| 20° | 76237 |
| 25° | 63028 |
| 30° | 49805 |
| 35° | 36995 |
| 40° | 25476 |
| 45° | 15971 |
| 50° | 8801 |
| 55° | 5161 |
| 60° | 4605 |
| 65° | 3943 |
| 70° | 3398 |
| 75° | 3474 |
| 80° | 2904 |
| 85° | 3019 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15971 cd/sqm



TEST NUMBER: P1302100

CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1GPH_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 44.6 | 10.5 |
| 10°-20° | 108.5 | 25.5 |
| 20°-30° | 118.9 | 27.9 |
| 30°-40° | 86.7 | 20.3 |
| 40°-50° | 40.9 | 9.6 |
| 50°-60° | 13.4 | 3.1 |
| 60°-70° | 7.6 | 1.8 |
| 70°-80° | 4.1 | 1.0 |
| 80°-90° | 1.3 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 272.0 | 63.9 |
| 0°-40° | 358.7 | 84.2 |
| 0°-60° | 413.1 | 97.0 |
| 0°-90° | 426.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 426.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 492 | |
| 5° | 480 | 45 |
| 15° | 390 | 108 |
| 25° | 260 | 119 |
| 35° | 138 | 87 |
| 45° | 52 | 41 |
| 55° | 14 | 13 |
| 65° | 8 | 8 |
| 75° | 4 | 4 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P1302100
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1GPH_3000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 492.3 |
| 2.5° | 489.4 |
| 5° | 479.5 |
| 7.5° | 464.2 |
| 10° | 443.8 |
| 12.5° | 419.2 |
| 15° | 390.5 |
| 17.5° | 359.5 |
| 20° | 326.7 |
| 22.5° | 293.3 |
| 25° | 260.5 |
| 27.5° | 227.7 |
| 30° | 196.7 |
| 32.5° | 166.8 |
| 35° | 138.2 |
| 37.5° | 112.4 |
| 40° | 89.0 |
| 42.5° | 68.5 |
| 45° | 51.5 |
| 47.5° | 37.5 |
| 50° | 25.8 |
| 52.5° | 17.0 |
| 55° | 13.5 |
| 57.5° | 11.7 |
| 60° | 10.5 |
| 62.5° | 8.8 |
| 65° | 7.6 |
| 67.5° | 6.4 |
| 70° | 5.3 |
| 72.5° | 4.7 |
| 75° | 4.1 |
| 77.5° | 2.9 |
| 80° | 2.3 |
| 82.5° | 1.8 |
| 85° | 1.2 |
| 87.5° | 0.6 |
| 90° | 0.0 |

(END OF REPORT)