

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300086

Luminaire Tested: P3AS17R25W2N902765DE010 E3PHLP1MW\_2700K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1300086  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R25W2N902765DE010 E3PHLP1MW\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,  
E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 624.0 lumens  
Efficiency: N/A  
Efficacy: 32.2 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300086  
CATALOG NUMBER: P3AS17R25W2N902765DE010 E3PHLP1MW\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1300086

CATALOG NUMBER: P3AS17R25W2N902765DE010 E3PHLP1MW\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90				90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81				81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74				74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68				68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63				63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	63	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55				55
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46				46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	209654
5°	198084
10°	168378
15°	133349
20°	101345
25°	75609
30°	54996
35°	38896
40°	26392
45°	18421
50°	15454
55°	14948
60°	15744
65°	16189
70°	16028
75°	17199
80°	19699
85°	19625

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 21000 cd/sqm



TEST NUMBER: P1300086

CATALOG NUMBER: P3AS17R25W2N902765DE010 E3PHLP1MW\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.2	13.0
10°-20°	162.6	26.1
20°-30°	144.0	23.1
30°-40°	91.7	14.7
40°-50°	48.5	7.8
50°-60°	35.7	5.7
60°-70°	30.3	4.9
70°-80°	21.4	3.4
80°-90°	8.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	387.8	62.1
0°-40°	479.5	76.8
0°-60°	563.7	90.3
0°-90°	624.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	624.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	956	
5°	900	81
15°	587	163
25°	312	144
35°	145	92
45°	59	49
55°	39	36
65°	31	30
75°	20	21
85°	8	8
90°	0	



TEST NUMBER: P1300086

CATALOG NUMBER: P3AS17R25W2N902765DE010 E3PHLP1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	956.1
2.5°	942.1
5°	899.9
7.5°	834.3
10°	756.2
12.5°	671.8
15°	587.4
17.5°	506.2
20°	434.3
22.5°	368.7
25°	312.5
27.5°	262.5
30°	217.2
32.5°	178.1
35°	145.3
37.5°	115.6
40°	92.2
42.5°	73.4
45°	59.4
47.5°	51.6
50°	45.3
52.5°	42.2
55°	39.1
57.5°	37.5
60°	35.9
62.5°	32.8
65°	31.2
67.5°	28.1
70°	25.0
72.5°	23.4
75°	20.3
77.5°	17.2
80°	15.6
82.5°	12.5
85°	7.8
87.5°	3.1
90°	0.0

(END OF REPORT)